

# Bronze Pedestal Self-Priming Centrifugal Pumps

**30PB Series** 

### Pipe Size 1" NPT



| Model    | Description                                  |
|----------|--|
| 30PB     | Stainless Steel Shaft & NBR Mechanical Seal  |
| 30PB-01  | Monel Shaft & NBR Mechanical Seal            |
| 30PBS-10 | Stainless Steel Shaft & FKM Mechanical Seal  |
| 30PBS-11 | Stainless Steel Shaft & PTFE Mechanical Seal |


#### **FEATURES:**

- Self-Priming to 6.1 meters Suction Lift
- Rugged Bronze Construction
- Heavy Duty Ball Bearings Suitable for Pulley Drive Applications
- Bronze Models with Monel Shaft (30PB-1) Ideal for Marine Service. (Air Conditioning, Bilge, and Sea Water Recirculating)
- Can Handle Most Difficult Solvents with Proper Seal Arrangement, FKM (S10) or PTFE (S11) available
- Body O-ring eliminates gasket problems

Up to 22 GPM water flow and suction lift of 15 feet without a foot or check valve (25 foot suction lift using a foot or check valve and a filled inlet line). A 1/2" pipe plug on the tank top is for initial filling of priming chamber and inlet line--pump priming is automatic thereafter. Pump seal is mechanical carbon face type mated to ceramic wear face for maximum durability. Other seal components are made of NBR with low swell characteristics for compatibility with a wide range of liquids including many chemicals and solvents. These pump models are widely used for the pumping of Perchloroethylene. Must be operated in the horizontal position. (As shown in picture)

#### **PERFORMANCE:**

CAPACITY WATER AT 60° F



#### Capacity - Water 60 F - Gallons per Minute

Maximum lift without foot valve is 10 feet

| Waximam int Without lost valve is 10 feet |      |                          |      |       |       |       |  |  |
|---|------|--------------------------|------|-------|-------|-------|--|--|
| Discharge Pressure                        |      | Suction Lift at 3450 RPM |      |       |       |       |  |  |
| Feet                                      | PSI  | 0 Ft                     | 5 Ft | 10 ft | 15 Ft | 20 Ft |  |  |
| 0   | 0    | 22                       | 20   | 17    | 14    | 10    |  |  |
| 5   | 2.2  | 20                       | 17   | 14    | 10    | 5     |  |  |
| 10  | 4.3  | 17                       | 14   | 10    | 5     |       |  |  |
| 15  | 6.5  | 14                       | 10   | 5     |       |       |  |  |
| 20  | 8.7  | 10                       | 5    |       |       |       |  |  |
| 25  | 10.8 | 5                        |      |       |       |       |  |  |
| 30  | 13   | 3                        |      |       |       |       |  |  |
| 35  | 15.2 | 1                        |      |       |       |       |  |  |

### **SEAL OPTIONS:**

(Note: Seal and shaft modifications below are not physically interchangeable. Consult factory for modification data.)


**FKM A Solvent Mechanical Seal:** Mechanical seal for oils, fuels, lubricants, most mineral acids, and many solvents that attack other rubbers such as Carbon Tetrachloride, toluene, benzene, and xylene.

**PTFE Mechanical Seal:** For virtually all industrial chemicals, corrosives and solvents - as limited by compatibility of basic pump metal of construction.

# **Bronze Pedestal Self-Priming Centrifugal Pumps**

**30PB Series** 


## **Exploded View**



### **Parts List**


|          | 1      | 2        | 3        | 4        | 5         | 6                  | 7         | 8      | 9      | 10     | 11              | 12                | 13       |
|----------|--------|----------|----------|----------|-----------|--------------------|-----------|--------|--------|--------|-----------------|-------------------|----------|
|          | Body   | Pedestal | Diffuser | Impeller | Seal Assy | Diffuser<br>Gasket | O-Ring    | Screw  | Plug   | Plug   | Ball<br>Bearing | Retaining<br>Ring | Lip Seal |
| Model    | Qty. 1 | Qty. 1   | Qty. 1   | Qty. 1   | Qty. 1    | Qty. 1             | Qty. 1    | Qty. 4 | Qty. 1 | Qty. 1 | Qty. 2          | Qty. 2            | Qty. 1   |
| 30PB     | 7190   | 7445     | 7192     | 7193     | 32155     | 6021-09            | 9797-157  | 5411   | 7321   | 7443   | 5928            | 5926              | 6609     |
| 30PB-01  | 7190   | 7445     | 7192     | 7193     | 32155     | 6021-09            | 9797-157  | 5411   | 7321   | 7443   | 5928            | 5926              | 6609     |
| 30PBS-10 | 7190   | 7445     | 7192     | 7193     | 32210     | 2271               | 9797-157  | 5411   | 7321   | 7443   | 5928            | 5926              | 6609     |
| 30PBS-11 | 7190   | 7777     | 7192     | 7193     | 32211     | 2271               | 9355-157S | 5411   | 7321   | 7443   | 5928            | 5926              | 6609     |

### **Dimensions**



|          | 14                | 15     | 16     | 17               | 18      | 19     | 20           |               |
|----------|-------------------|--------|--------|------------------|---------|--------|--------------|---------------|
|          | Retaining<br>Ring | Shaft  | Key    | Shim             | Slinger | Tag    | Tag<br>Screw | Repair<br>Kit |
| Model    | Qty. 1            | Qty. 1 | Qty. 1 | Varies           | Qty. 1  | Qty. 1 | Qty. 2       |               |
| 30PB     | 5925              | 7037   | 6567   | 602501, 02 or 03 | 7447    | 9344   | 9345         | 10865         |
| 30PB-01  | 5925              | 6890   | 6567   | 602501, 02 or 03 | 7447    | 9344   | 9345         | 10865         |
| 30PBS-10 | 5925              | 7037   | 6567   | 602501, 02 or 03 | 7447    | 9344   | 9345         | 11290         |
| 30PBS-11 | 5925              | 7037   | 6567   | 602501, 02 or 03 | 7447    | 9344   | 9345         | 12414         |

Item numbers 4, 5, 6, 7 & 17 are included in repair kit. Items 19 & 20 are not depicted above.





NBR = Acrylonitrile-Butadiene

# **BERDORFER PUMPS**

by Gardner Denver

5900 Firestone Drive, Syracuse, NY 13206

Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561

Visit www.oberdorferpumps.com to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.