



INDUSTRIAL | 5 HP ROTARY SCROLL AIR COMPRESSORS

## EnviroAire S5

Gardner Denver EnviroAire compressors provide the reliable, high quality compressed air that you've come to expect from Gardner Denver. EnviroAire compressors offer a wide selection of configurations and top-quality available options. Gardner Denver designed this series specifically for industrial and laboratory applications that require 100% oil-less air. Experience proven results with Gardner Denver—the leader in durability, reliability and efficiency.

### Standard Equipment

- Continuous operation, 100% duty cycle
- 5 Micron industrial grade intake air filter
- ASME coded receiver
- Premium efficient TEFC motor
- Unique tip seal design
- Low sound levels and vibration
- Re-greasable bearings
- Integral cooling fan
- Easy accessibility for maintenance
- 1-Year package warranty
- 1-Year airend warranty

### Available Options

- Tank Sizes—30, 80, 120 or 240 gallon
  - Galvanized receiver
  - Vinyl (epoxy) lined receiver
- Electronic tank drain
- Mass. code fittings
- Starter
- High temp switch
- Dryer options
  - Refrigerated dryer
  - Desiccant dryer

**Gardner**  
**Denver**

## BARE AIREND

MODEL	DIMENSIONS L x W x H IN.	APPROX. SHIP WEIGHT LBS
SC5	13.6 x 14.7 x 11.4	45

## SIMPLEX

MOTOR HP	BASE OR TANK CAPACITY GAL.	IDENTIFICATION NUMBER	DIMENSIONS L x W x H IN.	APPROX. SHIP WEIGHT LBS	116 PSI RATING		140 PSI RATING	
					RPM	ACFM	RPM	ACFM
5	Base	BENV55	38 x 21 x 17	260	3100	13.9	2900	12.5
5	30	HENV55-3	43 x 24 x 38	535	3100	13.9	2900	12.5
5	80	HENV55-8	67 x 24 x 42	660	3100	13.9	2900	12.5
5	120	HENV55-12	71 x 27 x 46	760	3100	13.9	2900	12.5

## DUPLEX

MOTOR HP	BASE OR TANK CAPACITY GAL.	IDENTIFICATION NUMBER	DIMENSIONS L x W x H IN.	APPROX. SHIP WEIGHT LBS	116 PSI RATING		140 PSI RATING	
					RPM	ACFM	RPM	ACFM
5	Base	BENVSD	48 x 22 x 36.5	713	3100	27.8	2900	25
5	80	HENV55D-8	65 x 26 x 61.5	1110	3100	27.8	2900	25
5	120	HENV55D-12	69 x 27 x 65.5	1210	3100	27.8	2900	25
5	240	HENV55D-24	86 x 33 x 71.5	1430	3100	27.8	2900	25

Simplex CFM values are doubled for duplex units. Duplex units have two motors and two pumps on one base/tank.

## TRIPLEX

MOTOR HP	BASE OR TANK CAPACITY GAL.	IDENTIFICATION NUMBER	DIMENSIONS L x W x H IN.	APPROX. SHIP WEIGHT LBS	116 PSI RATING		140 PSI RATING	
					RPM	ACFM	RPM	ACFM
5	Base	BENV55T	48 x 22 x 54.5	1062	3100	41.7	2900	37.5

Simplex CFM values are tripled for triplex units. Triplex units have three airends and three motors stacked on a common base.

## QUADRAPLEX

MOTOR HP	BASE OR TANK CAPACITY GAL.	IDENTIFICATION NUMBER	DIMENSIONS L x W x H IN.	APPROX. SHIP WEIGHT LBS	116 PSI RATING		140 PSI RATING	
					RPM	ACFM	RPM	ACFM
5	Base	BENV55Q	48 x 22 x 72	1415	3100	55.6	2900	50

Simplex CFM values are quadrupled for Quadraplex units. Quadraplex units have four airends and four motors stacked on a common base.

# Gardner Denver®

**Gardner Denver, Inc.**

1800 Gardner Expressway  
Quincy, IL 62305  
866-440-6241

[www.gardnerdenver.com/gdproducts](http://www.gardnerdenver.com/gdproducts)



©2017 Gardner Denver, Inc. Printed in U.S.A.  
GLCS-ENV-IND-S5 2nd Ed. 2/17

Please recycle after use.