

by Gardner Denver

# Ductile Iron Close Coupled Rotary Gear Pumps C9941B2 • C994R1B2

## 3/4" Ports Standard



#### **FEATURES:**

- Ductile Iron construction with steel shafts
- Stainless helical gears for quiet operation
- Two lip seals for added leak protection
- Self lubricating carbon bearings
- O-ring seal for maximum leak protection
- Durable temperature-resistant paint finish
- Easy field assembly to C-face motors
- Compact dimensions

## **GENERAL DESCRIPTION:**

Tailored specifically for wear resistance and long life in waste cooking oil transfer/reclamation service. They are designed to handle oil at elevated temperatures to 400° F, at pressures up to 50 psi, and at shaft speeds to 1750 RPM while tolerating warm water flush cycles. Shafts are hardened steel. Gears are 416 stainless steel. Rugged ductile iron housings incorporate body/gear lubrication grooves. High grade carbon-graphite bearings are used. The compact dimensions allow drop-in replacement for HYPRO - NG11 pumps.

#### **DRIVE:**


These close-coupled pumps mount directly to a full range of NEMA and IEC C-face motors by means of a suitable adapter bracket. The pump drive shaft is connected to the motor shaft by a flexible coupling. Complete pump and motor units are available.

#### **SEAL:**

Superior to mechanical seal designs that cannot tolerate occasional particles. Two independently mounted fluorocarbon lip seals are separated by an intermediate chamber. The chamber is filled with food grade grease to lubricate the outboard seal. Pumps are conveniently supplied with a grease fitting (an optional grease cup is available) to allow the addition of lubricant to the chamber during operation.

## **PERFORMANCE:**

Water 70° F




**SUCTION LIFT:** 

These positive displacement external gear pumps will generate 23" HG lift, a feature found to be essential for years of successful cycling. As a general rule, place the pump as close to the liquid source as possible. For a first start-up, the pump should be primed to avoid dry running. Minimum size of the suction pipe is the size of the pump inlet port. For longer suction lines (over 3 feet), the pipe size should be at least one size or two sizes larger than the pump inlet port.

## **ROTATION AND RELIEF VALVE:**

Given the body/gear face lubrication slots, these pumps are unidirectional. The standard pump is set up for normal rotation (clockwise when viewing the pump from the shaft end). Contact the factory if opposite rotation is required.


C994R1B2 is equipped with an integrated relief valve set up for internal bypassing. This relief valve is not intended to be a metering or flow control device. Its purpose is to function as a discharge pressure relief to guard against intermittent down stream system restrictions. Overheating can occur within 5 to 10 minutes if the discharge line is completely shut off. The relief valve is located on the discharge side of the pump. The pressure relief setting is not set at the factory. To increase pressure, turn the relief valve adjusting screw in a clockwise direction.



 $\ensuremath{\mathsf{WARNING}}$  : This pump is not NSF certified and not intended for sanitary filtration service.

# **Ductile Iron Close Coupled Rotary Gear Pumps**

C9941B2 • C994R1B2




	1	2	3	4	5	6, 7, 8	9	10	11	12	13	14	15	16	17	18
	Body	Cover	Drive Shaft	Drive Gear	Key	ldle Gear Assy.	Lip Seal	Bearing Carbon	Bearing Pin	Bearing Ball	Ret. Ring	Ret. Ring	Ret. Ring	Dowel Pin	O-Ring	Screw
Model	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 2	Qty. 3	Qty. 3	Qty. 1	Qty. 1	Qty. 2	Qty. 3	Qty. 2	Qty. 1	Qty. 8
C9941B2	9320UEZN	9322UN5N	2785	2888F	6567	33181	9354-03	2688	2687	2461	7557	5382	5464	8885	9797-041	5385
C994R1B2	9320UEZN	9323UN5B	2785	2888F	6567	33181	9354-03	2688	2687	2461	7557	5382	5464	8885	9797-041	5385

	19	20	21	22	23	24	25	26	27	28	29
	Grease Fitting	Pipe Plug	Stick Screw	Тад	Bypass But	Adjust. Screw	Fiber Washer	Locknut	Spring	Plugnut	Ball
Model	Qty. 1	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 1	Qty. 3	Qty. 1	Qty. 1	Qty. 1	Qty. 1
C9941B2	5390	2052	9345	9344	NA	NA	NA	NA	NA	NA	NA
C994R1B2	5390	2052	9345	9344	5200	5200	2692	5209	5207	5205	5206

\* Repair Kit #12211 contains items 10-20 & 27

\*\* Grease cartridges (Part # 2001) are available

# Dimensions





5900 Firestone Drive, Syracuse, NY 13206 Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561 Visit **www.oberdorferpumps.com** to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Adapter Kit

Н

J

G

т

Part #

11299C

11300C

11380 11386 Description

56C Frame 143TC/145TC

IEC 71

IEC80

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.