

A Gardner Denver Product

Bronze Close Coupled Rotary Gear Pumps

Model N1100

1 1/4" NPT Ports Standard



Refer to Model No. N11HDL for pedestal model and performance at different speeds.

Pump No.	Description		
N1100	Pump Only		
N1100W Pump, bracket and hardware for mounting to 56C frame motor			
N1100X	Pump, bracket and hardware for mounting to the following motor frames: 143TC, 145TC, 182C, 184C		
N1100Y	Pump, bracket and hardware for mounting to the following motor frames: 182TC, 184TC, 213C, 215C		
N1100Z	Pump, bracket and hardware for mounting to the following motor frames: 213TC, 215TC		

PSI	GMP	HP Reg.	HP Motor	HP Frame		Motor No.	
					Single Ph.	Three Ph.	
0	40	0.8	1	145TC	N1100XN46	N1100XN96	
10	39	0.9	'	14310	1411007140		
20	38	1.1	1 1/2	145TC	N1100XT46	N1100XT96	
30	37	1.4	1 1/2	14510	N1100X146		
40	36	1.7	2	184TC	N1100YW46	N1100W96	
50	35	2		10410	N 1100 1 W46		
60	34	2.3		213TC	N1100ZY46	N1100ZY96	
70	33	2.6	3				
80	32	2.8					
90	31	3.2					
100	30	3.5	_	5 213TC		N111007V06	
125	28	4.3	э			N1100ZX96	
150	25	5					

Note: Motors listed have ODP enclosures and the following electrical requirements: Single Phase: 115/230V, 60HZ

Single Phase: 115/230V, 60HZ Three Phase: 230/460V, 60HZ

FEATURES:

- Bronze Construction with Stainless Steel Shafts
- Positive Spring Loaded Lip Seal made from Viton®*
- Available with Motor Adapter and Hardware
- Easy Field Assembly to Motors
- Self-Lubricating Carbon Bearings
- Consult Factory for Special Motors

LIQUIDS AND TEMPERATURE:

Service life will be increased substantially if liquid pumped is clean and has lubricity value. These pumps have extremely close tolerance. Fine abrasives like sand, silt, or powders in suspension will destroy pumping ability.

Liquids compatible with bronze, stainless steel, and a $Viton(R)^*$ lip seal can be pumped. Check a chemical compatibility chart or Oberdorfer factory. Buna Lip Seal (S3) available.

Temperature extremes are detrimental to service life and should be avoided. Temperature range for this pump is from -20°F to 300° F. Freezing liquid in the pump can deform or damage the pump.

DRIVE:

The pump is driven directly from the electric motor shaft by means of a flexible coupling. An aluminum adapter connects the pump to the motor.

SUCTION LIFT:

A rotary gear pump is capable of lifting water on the suction side as high as 20 feet. Though gear pumps are self-priming, a foot valve is recommended. If possible, wet gears with the liquid to be pumped for the first dry start. Liquid retained in the system and gear chambers serves to wet the pump on subsequent starts.

ROTATION:

The pump or pump/motor unit is supplied by the factory for shaft rotation in either direction. Reversing the motor rotation will reverse the "in" and "out" ports.


To reverse single phase motors, find instructions on the inside of junction box cover or on name plate of motor.

Three phase motors are not wired for any particular rotation. They can be reversed by interchanging any 2 wires of the 3 wire leads.

Bronze Close Coupled Rotary Gear Pumps

Model N1100

Exploded View and Parts List



	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
	Cover	Cover Screws	Bearing	Idle Shaft	Drive Shaft	ldle Gear	Drive Gear	Dowel Pins	O-RIng	Body	Ret. Ring	Lip Seal	Ret. Ring	Key	Adapter Kit
Model	Qty. 1	Qty. 8	Qty. 4	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 4	Qty. 1	Qty. 1	Qty. 2	Qty. 1
N1100	9333NN5N	5393	5108	7652	8720	9834	9833	8597	9797-158	9330NG3N	7651	7262	7345	6518	See Below
N1100S3	9333NN5N	5393	5108	7652	8720	9834	9833	8597	9797-158	9330NG3N-0	7651	6500	7345	6518	See below


^{*} Repair Kit #11581 contains items 3, 4, 5, 6, 7, 9, 11, 12, 13, 14

Example

N1100	Υ	W96
Basic Pump	Mounting Adapter Kit (fits 184TC Motor Frame)	2HP 3 Phase Motor Code

Kit Code	Kit No.	Will Fit NEMA Motor Frames	Motor Flange Dea. Ref.	Motor Shaft Dia. Ref.	"A"	"B"
W	11617	56C	4.5	5/8	7.56	10.68
Х	11608	143TC, 145TC, 182C, 184C	4.5	7/8	7.56	10.68
Y	11609	182TC, 184TC, 213C, 215C	8.5	1 1/8	8.38	11.50
Z	11610	213TC, 215TC	8.5	1 3/8	8.38	11.50

Dimensions



Motor Data

Horse Power	Motor Code	Single Phase Part No.	Three Phase Part No.	NEMA Frame Size		
1	N46	8478		145TC		
'	N96		8480	145TC		
1 1/2	T46	8549		145TC		
1 1/2	T96		8486	145TC		
2	W46	8548		184TC		
2	W96		8490	184TC		
3	Y46	5846		213TC		
3	Y96		8547	213TC		
5						
ວ	X96		8689	213TC		

OBERDORFER PUMPS

A Gardner Denver Product

5900 Firestone Drive, Syracuse, NY 13206

Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561

Visit **www.oberdorfer-pumps.com** to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.