

## CHEMSTEEL®

### CHEMSTEEL SERIES S203 NON- METALLIC



A full range of accessories are available including: kits for base mounting, or close-coupling, line mount relief valves.

#### **GENERAL DESCRIPTION**

Chemsteel pumps are designed to handle common and highly corrosive liquids that must be pumped under pressure. Manufactured to extremely precise tolerance, the Chemsteel pump line prevents system contamination while maintaining the purity and integrity of the liquid being pumped. Its rugged, three-section construction provides ease of servicing and parts replacement.

Helical gearing offers noise reduction by as much as 10db, while the tandem pumps double the output flow for a single fluid, or with isolation, handle other fluids in direct ratio to the first.

Additionally, Chemsteel pumps offer bi-directional operation for applications requiring reversing flow.


#### LIFE CYCLE/COST OF OWNERSHIP

Pump design and materials selection, together provide the longest life available from a gear pump.

#### Key attributes include:

- Gear & bearing combinations of metallic and nonmetallic wear surfaces.
- Slotted bearings to lubricate shaft and gear surfaces.
- Hydraulic porting to balance axial thrust and to reduce wear.
- Ample port sizing to reduce the likelihood of cavitation when inlet pressure is marginal.
- Effective housing seals with elastic memory prevent leakage of corrosives.

#### **PERFORMANCE**



Notes: For continuous service:

Plastic / Plastic gear combinations are limited to 50 psi. Metal / Plastic gear combinations are limited to 100 psi. Horsepower requirements increase for viscous fluids.

#### **SPECIFIC SOLUTIONS**

Gear/bearing design allows for "trimming" for optimizing the pump's maximum flow to reach minimum turndown or to match flow to a specific OEM's requirement. Special materials combinations are available for specific

- Reinforced Ryton® housing construction.
- Gears available in metallic 316 stainless steel and Alloy C. Also in Teflon®, Ryton® and PEEK®.
- Shafts are 316 stainless steel or Alloy C.
- Bearings available in carbon or Teflon®. Full range of seal options including lip seal, packing and mechanical designs.

#### FIT

liquids:

Connections are female NPT or BSPT, pump hardware is metric and close couple adapters mount to both NEMA and IEC standard motor frame sizes for world wide acceptance.



#### **MAINTENANCE**

A three-part housing provides easy disassembly and service. Full size bearings match the gear diameter, and eliminate the need for separate wear plates. TFE encapsulating silicone pump housing seals provide elastic memory to assure an effective long lasting seal and thus avoiding the re-torquing required of pumps using pure TFE. The upper shaft configuration lends itself to in-line pump seal maintenance without the leakage of trapped chemicals from an incompletely drained pump.

To order a **CHEM**kit, simply add a "K" to the end of the model number. A repair kit contains the following parts: seals, bearings, gears, o-rings, shafts, keys, c clips, and retaining ring.

MODEL	S203 NM
maximum flow (gpm) @1750 rpm	1.5
theoretical displacement (cc/revolution)	4.2
maximum differential pressure (psig)	100
maximum system pressure (psig)	200
maximum speed (RPM)	1800
maximum fluid temperature	200° F
minimum fluid temperature	-40° F
standard port size	1/2 inch FNPT
weight (lbs)	3


# CLOSE-COUPLED DIMENSIONAL CAPACITOR CASE AND GASKET WHEN REQUIRED CONDUIT BOX WHEN REQUIRED LOCATION MAY VARY

mounted adapter code	kit part no.	mo fra	otor me		D1	2E	2F	Н	1	[1] <b>AP</b>	[] xo	AA	AB	1 AC	AD	AE		
C1	M2AD56R	D56R 56C		ECC		INCHES	3.50	4.88	3.00	ø.34 SLOT	6.88	6.63	2.25	7.14	9.66	18.04	_	9.71
	WZADSOK	36	30	MILLIMETERS	88.9	124	76.2	ø8.6 SLOT	174.8	168.4	57.2	181.4	245.4	458.1	-	246.6		
- 00		4.4070	44570	INCHES	3.50	5.50	4.00 5.00	ø.34 SLOT	6.88	6.63	2.25			19.23 20.73		9.53		
C2	M2AD45TR	143TC	145TC	MILLIMETERS	88.9	139.7	102 127	ø8.6	174.8	168.4	57.2	7.14	9.66	488.4 526.5	-	242.1		
	IVIZAD451K	4000	1010	INCHES	4.50	7.50	4.50 5.50	ø.41 SLOT	8.69	7.88	2.38			21.95 21.17		10.03		
		182C	184C	MILLIMETERS	114.3	190.5	114.3 139.7	ø10.41 SLOT	220.7	200	60.3	181.4	345.4	557.5 537.7	-	254.8		
C3	M2AD71RE	IEC 71 B	314 FACE	INCHES	2.80	4.41	3.54	ø.28 SLOT	5.14	4.69	_	6.64	9.16	18.47	4.00	8.42		
	WEAD! IKE	ILO 71, L	714 I AGE	MILLIMETERS	71	112	89.9	ø7 SLOT	130.6	119.1	_	168.7	232.7	469	102	213.9		
C4	M2AD80RE	IEC 80. B14 FACE		INCHES	3.15	4.92	3.94	ø.39 SLOT	6.00	5.69	_	6.64	9.16	18.70	4.51	8.62		
	IVIZADOUNE	IEC 00, E	14 FACE	MILLIMETERS	80	125	100.1	ø10 SLOT	152.4	144.5	_	168.7	232.7	474.9	116	218.9		

<sup>1.</sup> These dimensions vary depending on hp, enclosure, speed and motor manufacturer. Specifications are subject to change without notification

#### PEDESTAL MOUNT DIMENSIONS

	Α	В	С		С		С		С		С		С		С		С		С		С		С		С		С		D	Е	F	G	Н	J	К		L	M	N	0	Р	R	S		T	
			Mechanical	Pack 1	Lip						Diameter	Standard drive	Lower drive							Mechanical	Lip	Mechanical	Lip																							
inches	0.50	0.50	1.21"	0.72	2.25	6.67	4.38	3.82	1.12	2.38	0.26	2.38	1.08	2.50	3.41	0.22	2.88	3.50	1.73	2.19	1.73	2.75"	1.73																							
millimeters		12.7	30.7	18.3	57.2	169.4	111.3	97.0	28.4	60.5	6.6	60.5	27.4	63.5	86.6	5.6	73.2	88.9	43.9	55.6	43.9	69.9	43.9																							



Teflon® is a registered trademark of DuPont, an equivalent fluoropolymer may be used. Ryton® is a registered trademark of Chevron Phillips Chemical, an equivalent polyphenylenesulfide may be used. PEEK® is a trademark of Victors, an equivalent polypherhetherkinston emay be used. Viton® is a trademark of Dupont Dow Elastomers, an equivalent fluoroelastomer may be used. Kalrez® is a trademark of DuPont Dow Elastomers, an equivalent perfluoroelastometer may be used. Grafoli® is a trademark of UCAR Carbon Technology, an equivalent may be used.