MAG-DRIVE CLOSE COUPLED RM100 SERIES



MAG-DRIVE CLOSE COUPLED SM200 SERIES



MAG-DRIVE CLOSE



COUPLED SM400 SERIES

MAG-DRIVE CLOSE

COUPLED SM900 SERIES



MAG-DRIVE CLOSE COUPLED SM200 SERIES



MAG-DRIVE CLOSE COUPLED RM100 SERIES



MAG-DRIVE CLOSE COUPLED SM400 SERIES



MAG-DRIVE CLOSE COUPLED SM900 SERIES





Chemsteel Hydraulic Range @ 1425 RPM 7.0 100 -6.0 5.0


5900 Firestone Drive, Syracuse, NY 13206 Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561

OBERDORFER PUMPS

by Gardner Denver

Chemsteel™ **General Overview**

Metric Version



Chemsteel™ Features:

- Flows from 1.7 to 90 LPM at 1425 RPM
- Pressure from 0 to 10.3 BAR
- Gear & bearing combinations of metallic and nonmetallic wear surfaces
- Slotted bearings to lubricate shaft and gear surfaces
- Hydraulic porting to balance axial thrust and to reduce wear
- Ample port sizing to reduce the likelihood of cavitation when inlet pressure is marginal
- Effective housing seals with elastic memory prevent leakage of corrosives
- Recirculation heat port versatility
- Containment can flush and drain connections
- 316 Stainless Steel
- Alloy C
- Non-Metallic Ryton
- Packing Lip Mechanical Seal-less
- **IEC Close Coupled Adapters**
- Accessories

www.oberdorferpumps.com