BRONZE OR ALUMINUM CLOSE COUPLED HELICAL ROTOR PUMP

PIPE SIZE 3/4



Pump No.	Motor *	Enclosure	Frame	Body Construction		
101	Pump Only		56	Aluminum		
101-J25	1/2 HP, 1 Phase, 115/230 V	ODP				
101-J54	1/2 HP, 3 Phase, 208-220/440 V	ODP				
101-M07	3/4 HP, 1 Phase, 115/230 V	ODP				
101-M51	3/4 HP, 3 Phase, 220/440 V	ODP				
1015						
101B	Pump Only		56	Bronze		
101B-J08	1/2 HP, 1 Phase, 115/230 V	TE				
101B-J25	1/2 HP, 1 Phase, 115/230 V	ODP				
101B-J54	1/2 HP, 3 Phase, 208-220/440 V	ODP				
101B-M07	3/4 HP, 1 Phase, 115/230 V	ODP				
101B-M51	3/4 HP, 3 Phase, 220/440 V	ODP				
101G			500	A1		
	Pump Only		56C	Aluminum		
101G-J97	1/2 HP, 3 Phase, 240/480 V	TE				
101G-M97	3/4 HP, 3 Phase, 230/460 V	TE				
101BG			500	December		
	Pump Only		56C	Bronze		
101BG-J97	1/2 HP, 3 Phase, 240/480 V	TE				
101BG-M97	3/4 HP, 3 Phase, 230/460 V	TE				

^{*} Other motors available

ELECTRIC MOTOR MOUNTING

This pump is supplied close coupled to electric motor or as a pump alone complete with attaching parts and instructions for mounting. Any 56 frame electric motor (or 56C frame) with 5/8 inch shaft diameter, 1725 R.P.M. and of horsepower rating as listed above can be used. The motor can be rigid or resilient mounted, sleeve or ball bearings, 50°C rise, capacitor start, counter-clockwise, rotation from shaft end. (For Gas Engine version, see models 111-UGY/111B-UGY)

FEATURES

- All Bronze or Corrosion Resistant Aluminum Construction
- Easily Mounted in Field to your own 56 Frame Motor & 56C for explosion-proof motors
- Carbon Face Mechanical Seal
- Quiet Running
- Can Handle Contaminated Liquids
- · Buna Stator and Stainless Steel Rotor

CHARACTERISTICS

The turning of the helical shaped rotor within the stationary stator creates a progressing cavity similar to a moving piston. Liquid is thus displaced generating a pumping action. Unlike piston pumping, extremely high pressure cannot be created because the stator is made of Buna N and is flexible. Because of this flexibility contaminated liquids can be handled.

Close fit of the rotor within the stator permits lifting of liquid on the suction side as high as 20 ft. High starting torque motors are recommended in order to overcome the high starting friction of the stator. The pump is relatively quiet.

ROTATION

This helical rotor design demands a single rotation - clockwise when facing the pump drive shaft. Pump rotation and "in" and "out" ports are indicated on the dimension diagrams on reverse side.

MATERIALS OF CONSTRUCTION

These pump housings and mounting brackets are made from cast aluminum or bronze alloy. The rotor is made from stainless steel with a hard chrome plate for improved wear properties. The stator is made from molded Buna N. The mechanical seal is a carbon and ceramic mechanical rotary face type for positive sealing.

LIQUIDS

The corrosion resistant alloys used are compatible with common liquids including water, water solutions, oils and many commercial chemicals. Severe solvents are not compatible with the Buna and should <u>not</u> be pumped.


CAPACITY - WATER 60^O F 1725RPM

Pressure P.S.I.	0	10	20	30	40	50	60	70	80	90	100
Flow G.P.M. (Water)	8 1/2	8	7 1/2	7	6 1/2	6	5 1/2	5	4 1/4	3 3/4	3 1/4
Electric Motor H.P.	1/2	1/2	1/2	1/2	1/2	1/2	1/2	1/2	3/4	3/4	3/4



BRONZE OR ALUMINUM CLOSE COUPLED HELICAL ROTOR PUMP

PARTS LIST




	1	2	3	4*	5*	6	7	10*	11	12	13	14	15	16*	17	18*	19*
Pump No.	Adapter	Body	Cover	Rotor	Stator	Drive	Universal	Seal	Ball	Foot	Collar	Retaining	Retaining	Gasket	Nut	Pin	Pin
Fullip No.	Bracket Body Cove	Covei	KOLOI	Statut	Shaft	Joint	Assem.	Bearing	FOOL Collai	Ring	Ring	Gasket	ivut	F (()	"		
	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd	1 Reqd
101 J25	5871	5873	5872	5890	5891	5875	5874	32156	5884	5881	5886	5885	6053	5882	6350	5888	5889
101 M07	5871	5873	5872	5890	5891	5875	5874	32156	5884	5881	5886	5885	6053	5882	6350	5888	5889
101B J25	7213	6897	6896	5890	5891	5875	5874	32156	5884	5881	5886	5885	6053	5882	6350	5888	5889
101B M07	7213	6897	6896	5890	5891	5875	5874	32156	5884	5881	5886	5885	6053	5882	6350	5888	5889

^{*} Repair Kit No. 10737 include these parts and compression plate tool for seal removal

20	21	22	23	24	25	26	27
Body	Nut	Plug	Screw	Key	Stud	Acorn Nut	Motor
1 Reqd	2 Reqd	1 Reqd	14 Reqd	1 Reqd	4 Reqd	4 Reqd	1 Reqd
5873	5597	5908	5897	5912	6349	6351	5918
5873	5597	5908	5897	5912	6349	6351	5913
6897	5597	5908	5897	5912	6349	6351	5918
6897	5597	5908	5897	5912	6349	6351	5913

DIMENSIONS



Pump No.	С	D	Е	F	G	Н	J	K	L	М	N	0	Р	R	S	Т
101 J25	13/16	4 9/16	11 7/8	18 1/2	2 1/16	10 7/32	1 1/16	3	11/32	1 9/16	3 1/2	6 1/2	8 9/16	11/32	4 7/8	1 3/16
101B J25																