PIPE SIZE: 3/8 HOSE CONNECTION IN

3/8 HOSE CONNECTION OUT
1/8 AIR VENT HOSE CONNECTION



Model 142-01A44 shown

GENERAL

These compact high speed centrifugal pumps are suited for a variety of industrial and commercial applications. They are particulary well suited for portable liquid cleaning machinery, laboratory use and spray installations.

The design's symmetry provides a wide range of configuration possibilities allowing ready customization of discharge port position and optional air vent orientation relative to the motor base. (see below)

PUMP & MOTOR FEATURES

- " Chemical resistant construction
 - Body and Adapter made of non-metallic glass reinforced Nylon 6/6
 - Impeller made of non-metallic glass reinforced PPS
- " Mechanical Seal Type 6A carbon/ceramic faces, viton elastomers
- " Barbed -Hose Connections
- " Static Buna O-Ring body/adapter seal
- " Integrated Air Vent prevents loss of prime
- ,, Compact and Lightweight
- ... Installation/Mounting Versatility port orientation
- ,, Universal Open Drip Proof Motors with internal fan cooling, UL, CSA
 - No 18 Wire leads 25" long
 - Low amperage
 - 120VAC, 240VAC (Optional: double insulation) and 12VDC versions.

INSTALLATION

Maximum fluid temperature is 200°F. Fluids must be compatible with viton seal elastomer. To promote long product life, assure that ambient air can circulate around the unit to prevent over-heating.

Ground metal frame motors. There is a #6-32 tapped hole ground connection provided on the end of metal framed motors.

Prevent air trapping in plumbing lines by avoiding loops. Use air vent fitting connection to purge air. Though capable of pulling slight vacuum, the pump performs best under flooded suction conditions when located for gravity feed.

(10,000 RPM)


							Optimum Efficiency Range					
HEAD	PSI		0	5	10	15	20	25	30	35		
	FT.HD.		0	11.5	23	34.6	46.2	57.7	69.3	80.8		
FLOW	GPM	Plugged Vent	2.2	2.2	2.1	1.9	1.6	1.2	0.7	0.3		
	GPM	With Bypass thru Vent	2.0	2.0	1.9	1.6	1.3	0.9	0.4			
CURRENT	AMPS	@ 120V	1.45	1.45	1.45	1.40	1.35	1.30	1.25	1.20		
	AMPS	@ 240V	0.80	0.77	0.75	0.73	0.70	0.68	0.63	0.60		

12 VDC Motor (7,000 RPM)

HEAD	PSI		0	5	10	15	20
	FT.HD.		0	11.5	23	34.6	46.2
FLOW	GPM	Plugged Vent	1.9	1.7	1.4	1.1	0.5
CURRENT	AMPS	@ 12V	1.35	1.34	1.33	1.31	1.29



EXPLODED VIEW AND PARTS LIST



1	2	3	4	5	6 *	7	8	9	10	11	12	13	14	15	16	17	18
SCREW	BODY	PLUG	VENT	IMPELLER	SEAL	SEAL	O-RING	NUT	ADAPTER	SLINGER	SCREW	BASE	MOTOR	MOTOR	SCREW	SCREW	VENT
CONLETT			FITTING	3	HEAD	SEAT]								CAP
6 Req'd	1 Req'd	1 Req'o	l 1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	2 Req'd	1 Req'd	1 Req'd	2 Req'd	1 Req'o	1 Req'd	1 Req'd	4 Req'd	2 Req'd	1 Req'd

Pump																			
142-		7819	7752	7835		9407	8174	807901	7818		8255	6651		8367					
142- 01		7819	7752		7799	9407	8174	807901	7818		8255	6651		8367					7879
142- 02																			
142- 08																			
142- 12																			
142- 56																			
142- 10		7819	7752		7799	9407	8174	807901	7818		8255	6651							7879
-	Motor	Ī																	
	A44									7823			7821		8370				
	A46															8516	8450	9200	
	A47															8517	8450	9200	
	A91														-	2057	8450	9200	
NI 4																			

Notes:


*adhesive used to mount seal head to adapter


Repair Kits: Kit #

 Adapter Kit *
 11228 includes items
 1,6,8,9,10,11,17

 Impeller Kit
 11178 includes items
 5,7,8

DIMENSIONS







	DIMENSIONS								
PUMP	Α	В	С	D					
142-01A44	1.54	2.32	1.71	6.25					
142-01A46	1.67	2.45	2.74	7.16					
142-01A47	1.67	2.45	2.74	7.16					
142-01A91	1.67	2.45	2.74	7.16					



AIR VENT FITTING

The optional air vent fitting prevents loss of prime that can occur due to entrapped air. It is factory installed with a disposable vent cap. Entrapped air can be encountered in applications where the liquid in the supply tank is completely exhausted. Air can be introduced to the system before the next tank filling. For best results, configure and install pump with air vent near the top.





Pump No	Wet I	End Features	Features Motor Features							
	Vent Turret	Body Orientation	Insulation	Ground	Nominal Speed	Voltage	Part #			
	or Plug Position	to Motor or Motor Base								
142- 01 A44	I	А		External	10,000	120V AC	8370			
142- 02 A44	I	G		External	10,000	120V AC	8370			
142- 08 A44	I	С		External	10,000	120V AC	8370			
142- 10 A44	I	J		External	10,000	120V AC	8370			
142- 12 A44	I	G		External	10,000	120V AC	8370			
142- 56 A44	I	Α		External	10,000	120V AC	8370			
						•	-			
142- 01 A46	I	Α	Double		10,000	120V AC	8516			
142- 02 A46	I	G	Double		10,000	120V AC	8516			
142- 56 A46	I	Α	Double		10,000	120V AC	8516			
142- 01 A47	I	Α	Double		10,000	240V AC	8517			
142- 02 A47	I	G	Double		10,000	240V AC	8517			
142- A91	III	А			7,000	12V DC	2057			