

Rotary Gear & Centrifugal Pumps

BETTER Service BETTER Quality BETTER Selection



It's all about the Service

- Extensive distributor network delivers local relationships, fast response and personal service
- Industry leader in lead time and on-time delivery expectations
- Parts and kits available to extend the life of your pump



- Recognized as a global industry leader with 150 years of manufacturing experience
- Our history, experience and reputation set us apart from the competition
- Quality products backed by warranties—we set the standard for excellence



It's all about the Selection

- Numerous technology styles to meet to provide solutions for your application
- Multiple gear, port sizes and seal options available
- Expert customer service to answer application questions

Bronze Pedestal Rotary Gear Pumps



- Bronze Corrosion Resistant Castings
- Special Cast Helical Bronze Gears
- Stainless Steel Shafts & Fasteners
- Heavy Duty Carbon Bearings (self lubricating)
- Formed Ring Seal Packing
- Optional Lip & Mechanical Seals available on most models

Bronze Close-Coupled Rotary Gear Pumps



- Bronze Corrosion Resistant CastingsSpecial Cast Helical Bronze Gears
- O-ring seal for maximum leak protection
- Heavy Duty Carbon Bearings (self lubricating)
- Lip & Mechanical Seals Available
- Eliminates Motor Alignment Problems



Carbonator Motor-Mounted Gear Pumps



- Automotive Repair
- Road De-icing
- Day Tanks/Fuel Transfer
- Chemical Processing & Mixing
- Preservative Application
- Fuel Conditioning
- Coolant Circulation
- Bilge Pumps
- Irrigation
- And Many More!







©2018 Gardner Denver, Inc. Printed in U.S.A. OB-IND-GEN 1st Ed. 1/18

5900 Firestone Drive Syracuse, NY 13206 800-448-1668

Gardner Denver, Inc.

oberdorfermail@gardnerdenver.com www.oberdorferpumps.com