

Gardner Denver

POSITIVE DISPLACEMENT

Industrial Blowers & Vacuum Pumps

BETTER *Service* BETTER *Quality* BETTER *Selection*



It's all about
the Service

- Extensive distributor network delivers local relationships, fast response and personal service
- Over 75 reliable distributors with factory trained technicians ready to serve you
- Parts, lubricants and other operating supplies available locally



It's all about
the Quality

- Recognized as a global industry leader with 150 years of manufacturing experience
- Our history, experience and reputation set us apart from the competition
- Quality products backed by extensive warranties—we set the standard for excellence



It's all about
the Selection

- More technology styles than anyone else in the industry
- Each technology provides unique solutions for your application
- We make it easy to select the right blower with QuickPik
- Try it now at www.GDQUICKPIK.com

PACKAGES

GD IQ-HE | BLOWER PACKAGE

Airflow to 5,625 cfm
Pressure to 36 psig

- Offers extended high pressure range
- High efficiency package
- Reduce energy bills
- AirSmart G2 controller

GD IQ | BLOWER PACKAGE

Airflow to 1,500 cfm
Pressure to 15 psig
Vacuum to 17 inHG

- Intelligent package engineered with innovation and quality
- Intensely quiet design (as low as 60 dBA)
- Integral AirSmart Controller provides component monitoring
- Backed by 150 years of proven results

GD IQ-RB | BLOWER PACKAGE

Airflow to 5,500 cfm
Pressure to 15 psig
Vacuum to 15 inHG

- Low pressure package
- Integrated RBS 15-165 tri-lobe blowers
- Low energy consuming electric motor
- Fixed speed operation



GD CycloBlower® H.E. Series | HELICAL SCREW - DSL

Airflow to 6,200 cfm
 Pressure to 36 psig
 Vacuum to 22 inHg

- Best-in-class energy efficiency
- Game-changing patented design
- Built with best-of-the-best components
- Flexible options & installation



GD CycloBlower® | HELICAL SCREW - DSL

Airflow to 6,700 cfm
 Pressure to 20 psig
 Vacuum to 17 inHg
 Wet Vacuum to 24 inHg

- Efficiency leader at higher pressure
- Quiet, shock-free compression
- Clean air & gas delivery
- Higher pressure & vacuum performance



GD HeliFlow® | HELICAL TRI-LOBE - DSL

Airflow to 4,500 cfm
 Pressure to 18 psig
 Vacuum to 17 inHg

- Innovative & revolutionary PD blower design
- Reduced noise by 4-7 dBA
- Superior overhung load capacity



GD TriFlow® | STRAIGHT TRI-LOBE - DSL

Airflow to 700 cfm
 Vacuum to 16 inHg


- Designed for reduced noise and pulsation
- Advanced oil/air seals for reliable air delivery
- Heavy-duty design for reduced downtime



GD-DV | STRAIGHT TRI-LOBE - DSL

Airflow to 6,200 cfm
 Vacuum to 27 inHg


- Deep vacuum applications
- Cool operation temperatures
- Patented air inlet design



GD RBS | STRAIGHT TRI-LOBE - DSL

Airflow to 14,570 cfm
 Pressure to 15 psig
 Vacuum to 15 inHg

- Tri-Lobe rotors offer quiet, efficient operation
- Robust design for reliability and peace of mind
- Optional flange mount for unsurpassed versatility



GD DuroFlow® | STRAIGHT LOBE - DSL

Airflow to 4,300 cfm
 Pressure to 15 psig
 Vacuum to 16 inHg

- Designed for dusty, abrasive environments
- Advanced oil/air seals for reliable air delivery
- One piece rotor/shaft for increased durability



GD Sutorbilt® | STRAIGHT LOBE - GREASE & DSL

Airflow to 26,000 cfm
 Pressure to 15 psig
 Vacuum to 16 inHg
 Wet Vacuum to 24 inHg

- Decades of proven results
- Legend, 4500, 8000 & Quiet Series
- Available with mechanical seals
- Most versatile blower available



It's all about you!

MARKETS SERVED INCLUDE

- | | |
|-----------------------------|--------------------|
| ■ Wastewater Treatment | ■ Dairy |
| ■ Pneumatic Conveying | ■ Power Generation |
| ■ Dry Bulk Handling | ■ Carpet Cleaning |
| ■ Chemical Processing | ■ Soil Remediation |
| ■ Industrial Vacuum Systems | ■ And many more! |

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
 Quincy, IL 62305
 866-428-4890

www.gardnerdenver.com/gdproducts

