

COMPRESSOR DATA SHEET

Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

| | | | |
|-----|--|--------------|-------------------------|
| 1 | Manufacturer: GARDNER DENVER | | |
| 2 | Model Number: ST G2 100hp, 150psi | Date: | 04/02/19 |
| | <input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled | Type: | Screw |
| | <input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free | # of Stages: | 1 |
| 3* | Rated Capacity at Full Load Operating Pressure ^{a, e} | 434 | acfm ^{a, e} |
| 4 | Full Load Operating Pressure ^b | 150 | psig ^b |
| 5 | Maximum Full Flow Operating Pressure ^c | 150 | psig ^c |
| 6 | Drive Motor Nominal Rating | 100 | hp |
| 7 | Drive Motor Nominal Efficiency | 95.4 | percent |
| 8 | Fan Motor Nominal Rating (if applicable) | NA | hp |
| 9 | Fan Motor Nominal Efficiency | NA | percent |
| 10* | Total Package Input Power at Zero Flow ^e | 19.9 | kW ^e |
| 11 | Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d | 88.5 | kW ^d |
| 12* | Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e | 20.4 | kW/100 cfm ^e |

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program:

www.cagi.org

NOTES:

- Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- Total package input power at other than reported operating points will vary with control strategy.
- Tolerance is specified in ISO 1217, Annex C, as shown in table below:



| Volume Flow Rate at specified conditions | | Volume Flow Rate | Specific Energy Consumption | No Load / Zero Flow Power |
|--|-----------------------|------------------|-----------------------------|---------------------------|
| m ³ / min | ft ³ / min | % | % | |
| Below 0.5 | Below 15 | +/- 7 | +/- 8 | +/- 10% |
| 0.5 to 1.5 | 15 to 50 | +/- 6 | +/- 7 | |
| 1.5 to 15 | 50 to 500 | +/- 5 | +/- 6 | |
| Above 15 | Above 500 | +/- 4 | +/- 5 | |

ROT 030