

COMPRESSOR DATA SHEET
Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: GARDNER DENVER		
2	Model Number: ST 200 hp, EBQ, 200 psi	Date:	April 20, 2012
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled	Type:	Screw
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free	# of Stages:	1
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}	582	acfm ^{a, e}
4	Full Load Operating Pressure ^b	200	psig ^b
5	Maximum Full Flow Operating Pressure ^c	200	psig ^c
6	Drive Motor Nominal Rating	200	hp
7	Drive Motor Nominal Efficiency	95.8	percent
8	Fan Motor Nominal Rating (if applicable)	5	hp
9	Fan Motor Nominal Efficiency	89.5	percent
10*	Total Package Input Power at Zero Flow ^e	28.7	kW ^e
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	173.4	kW ^d
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e	29.8	kW/100 cfm ^e

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

- NOTES:
- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
 - b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
 - c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
 - d. Total package input power at other than reported operating points will vary with control strategy.
 - e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m ³ / min	ft ³ / min	%	%	+/- 10%
Below 0.5	Below 15	+/- 7	+/- 8	
0.5 to 1.5	15 to 50	+/- 6	+/- 7	
1.5 to 15	50 to 500	+/- 5	+/- 6	
Above 15	Above 500	+/- 4	+/- 5	

ROT 030

