



**COMPRESSOR DATA SHEET**  
**Rotary Compressor: Fixed Speed**

**MODEL DATA - FOR COMPRESSED AIR**

1	Manufacturer:	<b>Gardner Denver</b>	
2	Model Number:	<b>L132 - 100 psig</b>	Date: <b>12/12/2018</b>
	<input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled		Type: <b>Screw</b>
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free	# of Stages:	<b>1</b>
3*	Rated Capacity at Full Load Operating Pressure <sup>a, e</sup>	<b>799.9</b>	acfm <sup>a, e</sup>
4	Full Load Operating Pressure <sup>b</sup>	<b>100</b>	psig <sup>b</sup>
5	Maximum Full Flow Operating Pressure <sup>c</sup>	<b>110</b>	psig <sup>c</sup>
6	Drive Motor Nominal Rating	<b>180</b>	hp
7	Drive Motor Nominal Efficiency	<b>95.4</b>	percent
8	Fan Motor Nominal Rating (if applicable)	<b>0.9</b>	hp
9	Fan Motor Nominal Efficiency	<b>72.0</b>	percent
10*	Total Package Input Power at Zero Flow <sup>e</sup>	<b>46.1</b>	kW <sup>e</sup>
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>d</sup>	<b>142.91</b>	kW <sup>d</sup>
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>e</sup>	<b>17.87</b>	kW/100 cfm <sup>e</sup>

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)

- NOTES:
- Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
  - The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
  - Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
  - Total package input power at other than reported operating points will vary with control strategy.
  - Tolerance is specified in ISO 1217, Annex C, as shown in table below:



Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m <sup>3</sup> / min	ft <sup>3</sup> / min	%	%	
Below 0.5	Below 15	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	15 to 50	+/- 6	+/- 7	
1.5 to 15	50 to 500	+/- 5	+/- 6	
Above 15	Above 500	+/- 4	+/- 5	

ROT 030