

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: Gardner Denver		
2	Model Number: L29 - 100 psig	Date:	3/10/2015
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled	Type:	Screw
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free	# of Stages:	1
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}	193.1	acfm ^{a, e}
4	Full Load Operating Pressure ^b	100	psig ^b
5	Maximum Full Flow Operating Pressure ^c	110	psig ^c
6	Drive Motor Nominal Rating	40	hp
7	Drive Motor Nominal Efficiency	92.4	percent
8	Fan Motor Nominal Rating (if applicable)	1.2	hp
9	Fan Motor Nominal Efficiency	82.5	percent
10*	Total Package Input Power at Zero Flow ^e	11.4	kW ^e
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	36.5	kW ^d
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e	18.9	kW/100 cfm ^e

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

- NOTES:
- Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
 - The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
 - Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
 - Total package input power at other than reported operating points will vary with control strategy.
 - Tolerance is specified in ISO 1217, Annex C, as shown in table below:



Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$\frac{m^3}{min}$	$\frac{ft^3}{min}$	%	%	
Below 0.5	Below 15	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	15 to 50	+/- 6	+/- 7	
1.5 to 15	50 to 500	+/- 5	+/- 6	
Above 15	Above 500	+/- 4	+/- 5	

ROT 030