



**COMPRESSOR DATA SHEET**  
**Rotary Compressor: Fixed Speed**

**MODEL DATA - FOR COMPRESSED AIR**

1	Manufacturer: <b>Gardner Denver</b>		
2	Model Number: <b>L75 - 100 psig</b>	Date:	<b>3/10/2015</b>
	<input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled	Type:	<b>Screw</b>
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free	# of Stages:	<b>1</b>
3*	Rated Capacity at Full Load Operating Pressure <sup>a, e</sup>	<b>475.4</b>	acfm <sup>a, e</sup>
4	Full Load Operating Pressure <sup>b</sup>	<b>100</b>	psig <sup>b</sup>
5	Maximum Full Flow Operating Pressure <sup>c</sup>	<b>110</b>	psig <sup>c</sup>
6	Drive Motor Nominal Rating	<b>100</b>	hp
7	Drive Motor Nominal Efficiency	<b>94.1</b>	percent
8	Fan Motor Nominal Rating (if applicable)	<b>0.9</b>	hp
9	Fan Motor Nominal Efficiency (230/460 V)	<b>71.8</b>	percent
10*	Total Package Input Power at Zero Flow <sup>e</sup>	<b>26.8</b>	kW <sup>e</sup>
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>d</sup>	<b>89.5</b>	kW <sup>d</sup>
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>e</sup>	<b>18.8</b>	kW/100 cfm <sup>e</sup>

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)

- NOTES:
- Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
  - The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
  - Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
  - Total package input power at other than reported operating points will vary with control strategy.
  - Tolerance is specified in ISO 1217, Annex C, as shown in table below:



Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$\frac{m^3}{min}$	$\frac{ft^3}{min}$	%	%	
Below 0.5	Below 15	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	15 to 50	+/- 6	+/- 7	
1.5 to 15	50 to 500	+/- 5	+/- 6	
Above 15	Above 500	+/- 4	+/- 5	

ROT 030