

**COMPRESSOR DATA SHEET**



**Federal Uniform Test Method for Certain Air Compressors Not Applicable**

**Rotary Compressor: Variable Frequency Drive**

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: <b>Gardner Denver</b>			
2	Model Number: <b>ENV TVS200 -145psi</b>		Date:	<b>06/26/20</b>
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type:	<b>Screw</b>
	<input type="checkbox"/> Lubricated	<input checked="" type="checkbox"/> Oil Free	# of Stages:	<b>2</b>
3*	Full Load Operating Pressure <sup>b</sup>	<b>145</b>	psig <sup>b</sup>	
4	Drive Motor Nominal Rating	<b>270</b>	hp	
5	Drive Motor Nominal Efficiency	<b>95.0</b>	percent	
6	Fan Motor Nominal Rating (if applicable)	<b>2</b>	hp	
7	Fan Motor Nominal Efficiency	<b>86.5</b>	percent	
8*	Input Power (kW)		Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	236.40		<b>1087.7</b>	<b>21.73</b>
	220.30		<b>1010.0</b>	<b>21.81</b>
	203.40		<b>921.7</b>	<b>22.07</b>
	186.20		<b>826.4</b>	<b>22.53</b>
	169.30		<b>731.0</b>	<b>23.16</b>
9*	Total Package Input Power at Zero Flow <sup>c, d</sup>		<b>26.8</b>	kW
	<div data-bbox="430 1003 1286 1503" data-label="Figure"> <p align="center"> <b>Note: Graph is only a visual representation of the data in Section 8</b>                      Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35                      X-Axis Scale, 0 to 25% over maximum capacity                 </p> </div>			
10				

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load Zero Flow Power
m <sup>3</sup> / min	ft <sup>3</sup> / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2