

# COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

**Rotary Compressor: Variable Frequency Drive**

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: <b>Gardner Denver</b>			
2	Model Number: <b>ENV TVS250 -125psi</b>		Date:	<b>06/26/20</b>
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type:	<b>Screw</b>
	<input type="checkbox"/> Lubricated	<input checked="" type="checkbox"/> Oil Free	# of Stages:	<b>2</b>
3*	Full Load Operating Pressure <sup>b</sup>	<b>125</b>	psig <sup>b</sup>	
4	Drive Motor Nominal Rating	<b>335</b>	hp	
5	Drive Motor Nominal Efficiency	<b>95.4</b>	percent	
6	Fan Motor Nominal Rating (if applicable)	<b>2</b>	hp	
7	Fan Motor Nominal Efficiency	<b>86.5</b>	percent	
8*	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>		Specific Power (kW/100 acfm) <sup>d</sup>
	305.10	<b>1536.2</b>		<b>19.86</b>
	267.30	<b>1373.7</b>		<b>19.46</b>
	231.70	<b>1190.1</b>		<b>19.47</b>
	187.10	<b>995.9</b>		<b>18.79</b>
	166.40	<b>801.6</b>		<b>20.76</b>
9*	Total Package Input Power at Zero Flow <sup>c, d</sup>		<b>25.1</b>	kW
10	<p style="text-align: center; font-size: small;">                     Note: Graph is only a visual representation of the data in Section 8                      Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35                      X-Axis Scale, 0 to 25% over maximum capacity                 </p>			

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
  - b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
  - c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
  - d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
- NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load Zero Flow Power
m <sup>3</sup> / min	ft <sup>3</sup> / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2