

COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

| MODEL DATA - FOR COMPRESSED AIR | | | | |
|---------------------------------|---|--|-------------------|--|
| 1 | Manufacturer: Gardner Denver | | | |
| 2 | Model Number: ENV TVS250 -145psi | | Date: | 06/26/20 |
| | <input type="checkbox"/> Air-cooled | <input checked="" type="checkbox"/> Water-cooled | Type: | Screw |
| | <input type="checkbox"/> Lubricated | <input checked="" type="checkbox"/> Oil Free | # of Stages: | 2 |
| 3* | Full Load Operating Pressure ^b | 145 | psig ^b | |
| 4 | Drive Motor Nominal Rating | 335 | hp | |
| 5 | Drive Motor Nominal Efficiency | 95.4 | percent | |
| 6 | Fan Motor Nominal Rating (if applicable) | 2 | hp | |
| 7 | Fan Motor Nominal Efficiency | 86.5 | percent | |
| 8* | Input Power (kW) | Capacity (acfm) ^{a,d} | | Specific Power (kW/100 acfm) ^d |
| | 298.90 | 1377.3 | | 21.70 |
| | 269.90 | 1250.1 | | 21.59 |
| | 240.40 | 1105.4 | | 21.75 |
| | 211.60 | 953.5 | | 22.19 |
| | 184.20 | 798.1 | | 23.08 |
| 9* | Total Package Input Power at Zero Flow ^{c, d} | | 27.6 | kW |
| 10 | <p style="text-align: center; font-size: small;"> Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity </p> | | | |

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

| Volume Flow Rate at specified conditions | | Volume Flow Rate | Specific Energy Consumption | No Load Zero Flow Power |
|--|-----------------------|------------------|-----------------------------|-------------------------|
| m ³ / min | ft ³ / min | % | % | % |
| Below 0.5 | Below 17.6 | +/- 7 | +/- 8 | |
| 0.5 to 1.5 | 17.6 to 53 | +/- 6 | +/- 7 | +/- 10% |
| 1.5 to 15 | 53 to 529.7 | +/- 5 | +/- 6 | |
| Above 15 | Above 529.7 | +/- 4 | +/- 5 | |

ROT 031.2