

ELECTRA SAVER II G2 40-60 HP ROTARY SCREW COMPRESSOR, 60 HZ

MODEL	DRIVE MOTOR		NOMINAL PRESSURE		FAD		NOISE LEVEL ¹	WEIGHT		DIMENSIONS L × W × H IN. (MM)
	HP	KW	PSIG	BAR	ACFM	M ³ /MIN	DB(A)	LBS	KG	
STG2-40	40	30	100	6.9	204	5.78	78	2098	952	
			125	8.6	192	5.44				
			150	10.3	162	4.59				
			175	12.0	148	4.19				
			200	13.8	137	3.88				
STG2-50	50	37	100	6.9	251	7.11	78	2164	982	70 × 52 × 47 (1778 × 1321 × 1194)
			125	8.6	233	6.6				
			150	10.3	213	6.03				
			175	12.0	191	5.41				
			200	13.8	170	4.82				
STG2-60	60	45	100	6.9	305	8.64	79	2404	1090	
			125	8.6	287	8.14				
			150	10.3	249	7.05				
			175	12.0	219	6.20				
			200	13.8	217	6.14				

1) Noise level, weights and dimensions are for unenclosed models.