

# Technical Specifications

Model	Motor Rating		Free Air Delivered m <sup>3</sup> /min			Dimensions (L x W x H)	Noise Level	Weight
	(kW)	(hp)	7.5 bar g	10 bar g	13 bar g	(mm)	db (A)**	(kg)
<b>BLE-07</b>	7.5	10	1.30	1.06	0.85	667 x 630 x 1050	68	205
<b>BLE-11</b>	11	15	1.82	1.61	1.32	667 x 630 x 1050	68	219
<b>BLE-15</b>	15	20	2.70	2.26	1.80	787 x 698 x 1202	69	335
<b>BLE-18</b>	18.5	25	3.25	2.74	2.34	787 x 698 x 1202	70	361
<b>BLE-22</b>	22	30	3.65	3.21	2.61	787 x 698 x 1202	70	367

\*Measured and stated in accordance with ISO 1217 Annex C and Pneurop/Cagi PN2OPTC2 at the following conditions: Air Intake Pressure - 1 bar a (14.5 psi.a), Air Intake Temperature - 20°C (68°F), Humidity - 0% (dry), Cooling Water Inlet Temperature - 20°C (68°F), \*\*+\_3 dB(A) according to Pneurop/Cagi test code.

**Gardner Denver – BLE07 – BLE22**