

Gardner Denver

DRY BULK, CHEMICAL, HYDRAULIC AND SANITARY EQUIPMENT

Mobile/Transport Products

Who We Are

Worldwide Industrial Manufacturer
Gardner Denver, Inc.
1800 Gardner Expressway
Quincy, IL 62305
www.GardnerDenver.com
Established in 1859

Where We Operate

- Division Headquarters: Milwaukee, WI
- Research and Development: Quincy, IL
- Manufacturing & Remanufacturing Facility: Sedalia, MO
- Sales & Service: Worldwide

Mobile/Transport Products

Gardner Denver is the only supplier to the industry that meets all your dry bulk, chemical, hydraulic and sanitary equipment needs.

Our product lines represent a proven history and reputation for quality, dependability and performance.

- CycloBlower®, DuroFlow®, Wittig®, Aqualine®, Drum products including Hydrapak®, Compressors, Vane and Lobe Blowers, and Food Pumps
- Gardner Denver is one of the world's largest manufacturers of positive displacement blowers, exhausters & vacuum pumps
- Our products are backed by extensive local and factory trained aftermarket service and support

What We Do

With 150 years of manufacturing experience, Gardner Denver is a recognized leader providing compressed air and gas, vacuum and fluid transfer technologies to industries throughout the world.

Why Gardner Denver

- Tradition
- Engineering
- Results
- Quality
- Service

Markets Served and Applications

- Dry Bulk Handling
- Food Grade Products
- Chemical Transfer
- Hydraulic Cooling
- Sewage Cleaning



GD CycloBlower® Transport Series



Helical Screw

Airflow to 1,060 cfm
Pressure to 18 psig
Vacuum to 17" Hg

- Efficiency leader at higher pressure
- Quiet, shock free compression
- Clean air & gas delivery
- Higher pressure & vacuum performance

GD D807/D907® Transport Series



Drum Lobe

Airflow to 1,300 cfm
Pressure to 20 psig
Vacuum to 17" Hg

- Up to 20 psig continuous duty operation (D807)
- Reduced noise and pulsation
- Easy maintenance

GD HPD450/E490® Transport Series



Drum Vane

Airflow to 325 cfm
Pressure to 30 psig

- 100% oil free air
- Robust and compact
- Low noise operation

MH Series Hydrapak®



Hydraulic Drive Cooling Systems

Flow rate to 60 gpm
Pressure rated to 3500 psi
Stainless steel construction

MH-C2 Series Hydrapak®



Hydraulic Drive Cooling Systems

Flow rate to 30 gpm
Pressure rated to 5000 psi
Stainless steel construction

- New patented narrow design is only 8.5" wide

GD DuroFlow® Transport Series



Rotary Lobe

Airflow to 1,000 cfm
Pressure to 15 psig
Vacuum to 15" Hg

Food Grade & Chemical Handling Series



GD150 Oil-Free Compressor

Radial Vane

Airflow to 75 cfm, speed to 1800 rpm
Pressure to 36 psig

- Fast discharge rates
- Low viscosity liquid discharge from multi-purpose tank-trucks and other tank containers
- Highly corrosion resistant, light weight

STP 125 Stainless Steel Food & Chemical Pump



Tri-Lobe

Flow to 232 gpm
Pressure to 140 psi

- Tri-Lobe impeller design for reduced noise and pulsation
- Ideal for Food-Grade Products Transfer

Wittig® Transport Series



Rotary Vane Compressors & Vacuum Pumps

Airflow to 377 cfm (RFL), 906 cfm (RFW), 341 cfm (RTL)
Pressure to 29 psig
Vacuum to 24" Hg (RFL & RFW)

- Wide range of installation options
- Simple to operate, robust with minimal maintenance

Aqualine Series



Liquid-ring compressor & Vacuum Pumps

Airflow to 1803 cfm
Pressure to 22 psig/Vacuum to 27" Hg

- Ideal for sludge handling
- Lightweight and compact

Gardner Denver

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenverproducts.com

