TurboTron®

REGENERATIVE BLOWERS/EXHAUSTERS




Full Flow and Half Flow

REGENERATIVE BLOWERS/EXHAUSTERS





Revolutionary Design



The patented Lamson® TurboTron® Regenerative Full Flow and Half Flow blowers/exhausters are specifically designed to provide continuous flow and pulse-free air with the versatility to perform in numerous air applications. These regenerative blowers/exhausters are packaged in various pre-engineered "TurboPak" systems and are available as belt drive, direct drive, overhung and even VFD variable speed configurations. Its unique capabilities make the TurboTron Regenerative blower the choice in applications from wastewater treatment aeration and pneumatic conveying to chemical tank agitation and vacuum cleaning. Typical industries for TurboTron regenerative blowers include foundries, plating, plastics, pharmaceutical, pulp and paper and printing.

Key Features

Installed as a blower or exhauster, the Lamson TurboTron Regenerative unit features a revolutionary impeller design, achieving multistage compression with a single impeller. This unique design represents the best efficiency available in a regenerative blower/exhauster. The TurboTron regenerative blower delivers quiet, clean, smooth, pulse-free air with pressures to 13 psig and vacuum to 14 "Hg.

Ouiet and Noise Free

Noise and vibration are reduced. Even without an acoustical cover, the typical free field noise level is only 82 dBA at three feet (one meter).

Trouble-Free

This regenerative blower/exhauster is virtually maintenance free. There is only one moving part and no timing gears. The high tensile strength aluminum composite housing is corrosion resistant. Non-binding Teflon® is used in close tolerance areas. Bearings require only occasional greasing, and shaft seals are non-contacting and non-wearing.

Value

A revolutionary design, proven dependability and power make this blower/vacuum producer the best investment for the most demanding applications. Application assistance is available by contacting your local Hoffman/Lamson representative.

Full Flow Series	Half Flow Series
Airflow to 900 cfm	Airflow to 450 cfm
Pressure to 13 psig	Pressure to 13 psig
Vacuum to 14 "Hg	Vacuum to 14 "Hg

TurboPak™

ENGINEERED SYSTEMS

TurboTron's Full Flow and Half Flow TurboPak A, C and VFD are pre-engineered packages that include a patented TurboTron regenerative blower/exhauster assembled with a motor on a heavy-duty platform.

TurboPak A Regenerative Blower/Exhauster Systems

TurboPak A is the economical and proven way to provide a constant flow of air at varying pressures.

TurboPak C Regenerative Blower/Exhauster Systems

TurboPak C adds a silencer base with integrated inlet and discharge silencers for improved sound attenuation.

TurboPak VFD Variable Speed Regenerative Blower/Exhauster System

The Gardner Denver TurboPak VFD is designed to greatly improve turndown capability at very low overall cost. The TurboPak VFD is particularly well suited to the varying air demands of post aeration in wastewater treatment plants.

TurboPak VFD - Value

A TurboPak VFD was teamed with a small multistage centrifugal blower and compared to four other scenarios to determine the lowest overall cost option for a post aeration project in New Jersey. The following table summarizes how the TurboPak VFD/Multistage option was the most cost effective with the highest turndown ratio based on 2200 SCFM/6 psig.


Power

Machine	Min Power (bhp)	Max Power (bhp)	Overall Turndown (%)	% Cost
TurboPak VFD and Multistage	17.0	100.9	92	100
Single Multistage	55.8	93.2	50	129
Two Multistage	36.8	109.0	70	136
Three Multistage	21.2	103.5	86	133
Single Multistage with VFD	34.3	114.3	64	173










TurboTron Specifications

TurboPak A

TurboPak C





FULL FLOW



	RPM		2	3	4	5	6	7	8	9	10	11	12	13
	2000	SCFM	262	211	164	120								
	2000	HP	5.1	7.1	9.1	11.1								
ŀ	2800	SCFM	458	415	374	333	295	257	221					
	2000	HP	9.0	11.7	14.3	17.0	19.7	22.5	25.2					
	3700	SCFM	668	629	591	555	520	486	454	423	393	364		
	3/00	HP	15.3	18.9	22.4	22.8	29.3	32.9	36.6	40.4	44.1	47.6		
1	4500	SCFM	858	817	780	745	713	682	653	626	600	575	552	529
	4500	HP	22.8	27.4	31.7	35.9	40.1	44.3	48.6	52.9	57.3	61.6	66.0	70.2

Pressure (psig)

Pressure (psig)

RPM		3	4	5	6	7	8	9	10	11	12	13	14	
2000	SCFM	258	217	179	143	109	77							g
2000	HP	3.8	4.8	5.8	6.8	7.7	8.7							工
2800	SCFM	428	393	352	312	274	235	199	163	128				
2800	HP	7.0	8.0	9.3	10.5	11.7	13.0	14.2	15.6	16.9				Ε
3700	SCFM	630	583	536	490	446	402	359	318	278	239			2
3700	HP	10.8	12.8	14.5	16.1	17.7	19.2	20.7	22.4	24.1	25.8			aci
4500	SCFM	810	757	702	648	596	546	498	452	407	364	323	283	Va
4300	HP	15.7	18.0	20.3	22.3	24.2	26.0	27.8	29.5	31.3	33.2	35.0	36.7	


RPM		2	3	4	5	6	7	8	9	10	11	12	13
2000	SCFM	131	105	82	60								
2000	HP	2.8	3.9	5.0	6.1								
2800	SCFM	229	208	187	167	147	129	111					
2000	HP	5.0	6.4	7.9	9.3	10.8	12.3	13.9					
3700	SCFM	334	314	295	277	260	243	227	211	196	182		
3700	HP	8.4	10.4	12.3	14.2	16.1	18.1	20.1	22.2	24.3	26.2		
4500	SCFM	429	409	390	373	356	341	327	313	300	288	276	265
4500	HP	12.5	15.1	17.4	19.7	22.0	24.3	26.7	29.1	31.5	33.9	36.3	38.6

В	RPM		3	4	5	6	7	8	9	10	11	12	13	14	
н	2000	SCFM	129	109	90	71	55	39							<u>6</u>
ı	2000	HP	2.1	2.6	3.2	3.7	4.2	4.8							I
1/	2800	SCFM	214	197	176	156	134	118	99	81	64				-
/-	2000	HP	3.9	4.4	5.1	5.8	6.4	7.1	7.8	8.6	9.3				<u>E</u>
5	3700	SCFM	315	291	268	245	223	201	180	159	139	119			n
1	3700	HP	5.9	7.0	8.0	8.9	9.7	10.6	11.4	12.3	13.2	14.2			ac
	4500	SCFM	4.5	378	351	324	298	273	249	226	203	182	161	141	>
	4300	HP	8.6	9.9	11.2	12.3	13.3	14.3	15.3	16.2	17.2	18.2	19.2	20.2	

Performance data for air at standard conditions:

Sea level, 14.7 PSIA, 29.92 "Hg, 68°F inlet temperature, 36% relative humidity.

HALF FLOW





Gardner

www.HoffmanandLamson.com in fo. hoffman lams on s@gardner denver.com

Gardner Denver Nash PO Box 130 Bentleyville, PA 15314 USA New Equipment Sales: (800) 543-7736 Aftermarket Parts Sales: (800) 982-3009 Phone: +1 724-239-1500 Fax: +1 724-239-1502







Specifications subject to change without notice. Please recycle after use.

