Compression Spring
Draw Bar Assembly
for Emco Wheaton
E2123 Long-Reach Bottom



Loading Arm

This retrofit spring is compatible with the Emco Wheaton E2123 Long-Reach Bottom Loading Arm.

Features and Benefits:

- · Can be retrofitted with minimal tools
- Draw bar design for failsafe redundancy
- Powder-coated for longer life expectancy
- Easily adjustable turnbuckle fastener design

Draw Bar:

- Material 17-4 Stainless
- Inside Loop Length 35" +/- .50
- Coating Powder Coat Red Finis

Compression Spring:

- Material Chrome Silicon Commercial / Wire Dia .562 in. +/- .0015
- Spring Rate 184 LB/IN
- Total Coils 26.0 +/- .25
- Load breaking capability 1381 LB @ 7.5" Deflection Ref
- Max Deflection/Load 9.3"/1715 LBF (Solid)
- Heat Treat Stress Relieve
- Shot Peen
- Coating Powder Coat Red Finish

How To Order:

Available from Emco Wheaton as a complete kit under part #E2123-RF2019

www.emcowheaton.com

