

by Gardner Denver

Bronze Close Coupled Rotary Gear Pumps

N992(R) DC Series





FEATURES:

- Compact design eases installation and use in limited space areas.
- Construction is bronze and stainless steel wetted components.
- Close tolerance design allows for consistent performance.
- Self-Lubricating Bearings
- Complete Units Available
- Slotted Motor Base
- Permanent Magnet Rigid Base Motors

GENERAL DESCRIPTION:

Pump housings and gears are made of top quality bronze, shafts are 303 stainless steel. Bearings are designed of high performance carbongraphite material selected for wear resistance and long service life.

Gear pumps are positive displacement pumps. Each shaft revolution displaces a definite amount of liquid relatively unaffected by the back pressure in the discharge line. Shaft speed and flow are directly proportional.

LIQUIDS AND TEMPERATURE:

Compact DC portable units convienient for on site servicing of vehicles, machinery and field equipment. For pumping oil direct from crankcase or oil resevoir, drums, containers, transfer diesel fuel to vehicles, pumping other liquids and chemicals compatible with materials of construction. Pumping viscous oils, SAE 30 or greater, can overload motor. Intermittent use is recommended when pumping viscous oils, especially in cold weather.

Service life will be increased substanially if liquid pumped is clean and has lubricity value. These pumps have extremely close tolerances. Fine abrasives like sand, silt or powders in suspension will destroy pumping ability. Liquids compatible with bronze, stainless steel and the NBR lip seal can be pumped. For solvents a FKM lip seal is available. For a FKM Seal, add S5 to the pump model number. See chemical compatibility table.

Temperature extremes are detrimental to service life and should be avoided. Basic metals of construction allow temperature range of -40° to 400° F. Standard NBR lip seal has a temperature limit of 250° F, while the FKM lip seal will handle up to 300° F. Freezing liquid in the pump can deform or damage the pump.

SUCTION LIFT:

As a general rule, the suction lift should be kept at an absolute minimum by placing the pump as close to the liquid source as possible. A gear pump in new condition can lift 20 feet of water in the suction line. A foot valve (preferably with builtin strainer) is recommended at the beginning of the suction line. For a first start-up, the pump should be primed to avoid dry running. Minimum size of the suction pipe is the size of the pump inlet port. For longer suction lines (over 3 feet) or for viscous liquids, the pipe should be at least one size or two sizes larger than the pump inlet port.

ROTATION AND RELIEF VALVE:

If the discharge line contains any throttling devices such as a shut-off valve, a spray nozzle or other restrictive device, it is necessary to have a relief valve in the system which returns the liquid to the suction side or to the tank. The relief valve is also available as part of the pump itself (R-model pumps). However, built-in relief valves are only good for intermittent service. If used continuously, the pump will overheat. A built-in relief valve is strictly a safety device against overpressure. It will not work successfully as a pressure or flow control device. For this purpose a separate relief valve in the pressure line must be used.

Unless otherwise specified, the pump motor unit is supplied by the factory for shaft rotation counterclockwise from shaft end. Reversing motor will reverse "in and "out" ports and also requires changing relief valve location. The relief valve is always on the inlet side of this pump series. The factory pressure setting is 50 PSIG. To increase pressure, turn the relief valve adjusting screw in a clockwise direction.

Bronze Close Coupled Rotary Gear Pumps

N992(R) DC Series

PERFORMANCE:

Capacity - Water 70° F

Pressure (P.S.I.)

Motor No.	Voltage	HP		5	10	15	20	25	30	35	40	45	50	55	60	70	80	90	100
C81			Flow (GPM)	2.8	2.7	2.7	2.6	2.5	2.4	2.3	2.2	2.1	2.1	2.0					
	12 VDC	1/4	Speed (RPM)	1140	1120	1100	1090	1070	1060	1040	1020	1000	990	970					
8295			Current (Amps)	4.5	5.5	6.4	7.4	8.7	9.5	10.7	12.4	13.4	14.4	15.7					
C82			Flow (GPM)	5.9	5.8	5.8	5.7	5.6											
	24 VDC	1/4	Speed (RPM)	2330	2310	2300	2280	2270											
8295			Current (Amps)	5.9	6.8	7.6	8.4	9.1											
C74			Flow (GPM)	5.3	5.1	5.0	4.9	4.7											
	12 VDC	1/4	Speed (RPM)	2020	2020	1990	1960	1920											
2924			Current (Amps)	12.5	12.5	14.3	16.5	18.2											
F93			Flow (GPM)	4.9	4.9	4.8	4.8	4.7	4.6	4.5	4.5	4.4	4.3	4.3	4.2	4.1			
	24 VDC	1/3	Speed (RPM)	1960	1950	1950	1930	1920	1910	1910	1900	1900	1890	1890	1870	1850			
3073			Current (Amps)	5.1	5.5	6.1	6.9	7.7	8.6	8.9	9.2	9.8	10.1	10.5	11.5	12.8			
J75			Flow (GPM)	4.7	4.7	4.6	4.5	4.4	4.4	4.4	4.3	4.3	4.2	4.2	4.1	4.0	3.8	3.7	
	12 VDC	1/2	Speed (RPM)	1860	1850	1840	1830	1830	1830	1830	1830	1820	1820	1820	1820	1790	1770	1750	
8562			Current (Amps)	10.8	10.8	12.4	14.1	14.8	15.4	16.3	17.5	18.9	20.3	22.5	23.9	31.5	34.5	38.2	
J76			Flow (GPM)	5.1	5.1	5.0	5.0	4.9	4.8	4.8	4.7	4.6	4.5	4.5	4.4	4.3	4.1	4.0	
	24 VDC	1/2	Speed (RPM)	2020	2020	2020	2010	2000	2000	1990	1990	1980	1980	1970	1950	1940	1920	1900	
8563			Current (Amps)	5.8	5.8	6.3	6.9	7.5	8.2	8.8	9.2	9.9	10.5	11.3	12.2	15.9	17.3	18.7	

	23#	24#	25#	26#	27	Adoptor Kit
Motor Number	Spider	Coupling Half	Bracket/Adapter	Screw	Motor	Adapter Kit
	Qty. 1	Qty. 1	Qty. 1	Qty. 4	Qty. 1	Qty. 1
C81	7839	7643	7602	5916	8295	12144
C82	7839	7643	7602	5916	8295	12144
C74	7839	7643	8335	5411	2924	11331
F93	7839	7643	8335	5411	3073	11331
J75	7839	7643	8335	5411	8562	11331
J76	7839	7643	8335	5411	8563	11331


[#] Adapter Kits contain items 23, 24, 25 & 26

Parts List

	1	2	3	4	5	6	7	8	9	10		
	Screw	Body	O-Ring	Dowel Pin	Bearing	Drive Gear Assy	ldle Gear Assy	Cover	Lip Seal	Coupling		
Model	Qty. 6	Qty. 1	Qty. 1	Qty. 2	Qty. 4	Qty. 2	Qty. 1	Qty. 1	Qty. 1	Qty. 1		
N992	7733	9306NC5N	9797-038	8885	5024	32994	32993	9308NN2N	5007	5604		
N992R	7733	9306NC5N	9797-038	8885	5024	32994	32993	9308NN3B	5007	5604		
N992S5	7733	9306NC5N	9797-038	8885	5024	32994	32993	9308NN2N	7580	5604		
N992RS5	7733	9306NC5N	9797-038	8885	5024	32994	32993	9308NN3B	7580	5604		

^{*} Repair Kits contain items 3, 5, 6, 7, 9 & 12






	11	12*	13	14	15	16	17	18	19	20	21	22	
	Screw	Lock Ring	Plug Nut	Ball	Spring	Adjust. Screw	Lock Nut	Nut Bypass	O-Ring	O-Ring	Name Tag	Tag Screw	Repair Kits
Model	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 2	
N992	5595	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	9344	9345
N992R	5595	N/A	N/A	1838	5238	1840	5237	5240D	5239	9797-019	9797-015	9344	9345
N992S5	5595	7626	7626	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	9344	9345
N992RS5	5595	7626	7626	1838	5238	1840	5237	5240D	5239	9797-019	9797-015	9344	9345

Bronze Close Coupled Rotary Gear Pumps


N992(R) DC Series

Dimensions


N992(R)Q-J75 & N992(R)Q-J76



N992(R)-C81 & C82



4X 1.22



Recommended wire size and length AWG wire size and maximum length in ft.										
12 VOLT DC	11 ft.	18 ft.	28 ft.	45 ft.						
24 VOLT DC	20 ft.	34 ft.	55 ft.	87 ft.						
32 VOLT DC	35 ft.	56 ft.	91 ft.	144 ft.						



OBERDORFER PUMPS

by Gardner Denver

5900 Firestone Drive, Syracuse, NY 13206

Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561

Visit **www.oberdorferpumps.com** to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.