

industry revolves around  hydrovane

## HV Series: hypac

From 5–10 hp, hypac hydrovane compressors are pre-packaged on a tank or on a tank with a dryer for a complete hassle free, easy to install system.

- 5–10 hp (Fixed Speed)
- 10 hp RS (Regulated Speed)
- 80 Gallon Receiver, 120 Gallon Option
- 100 or 150 PSIG
- Optional Refrigerated Air Dryer
- Stainless Steel Tubing
- Small Footprint
- Enclosed Forklift Slots
- Standard 2 Year Warranty
- Platinum 10 Year Warranty Available
- hypac with Dryer Includes Standard 3-way Bypass and Integrated Grade B Filter
- Optional Grade E Cold Coalescing Filter



## We Build it. We Trust it. We Stand Behind it.

Every hydrovane is backed with a standard 2 year warranty, providing you with peace of mind when it comes to your system's operation.

### Not Enough?

Take advantage of our 10 year extended warranty program. Simply stated, it's the best plan in the industry.





## HV Series: hypac

hp	kW	Model	Voltage/Phase	Mounting Config.	Tank Style	Tank Cap. (Gal.)	CFM 100 PSIG	CFM 150 PSIG	Noise Level (dBA)	Air Outlet NPT	Oil Cap. (Gal)	Weight (lbs.)	L (in.)	W (in.)	H (in.)	Starter	After cooler
5	4	HV04	208-230 1Ph 200-230/460/575 3Ph	Tank	Horiz.	80	20.0	17.4	66	.75"	1	769	55.2	32	71.1	Yes	Yes
7.5	5	HV05	208-230 1Ph 200-230/460/575 3Ph	Tank	Horiz.	80	30.5	21.5	66	.75"	1	780	55.2	32	71.1	Yes	Yes
10	7	HV07	200-230/460/575 3Ph	Tank	Horiz.	80	36.6	29.4	67	.75"	1	804	55.2	32	71.1	Yes	Yes
10	7	HV07RS	460 3Ph	Tank	Horiz.	80	37.1 @ 115 PSIG	34.8	67	.75"	1	820	55.2	32	71.1	Yes	Yes

\*120 gallon tank optional



## HV Series: hypac with dryer

hp	kW	Model	Voltage/Phase	Mounting Config.	Tank Style	Tank Cap. (Gal.)	CFM 100 PSIG	CFM 150 PSIG	Noise Level (dBA)	Air Outlet NPT	Oil Cap. (Gal)	Weight (lbs.)	L (in.)	W (in.)	H (in.)	Starter	After cooler
5	4	HV04	208-230 1Ph 200-230/460/575 3Ph	Tank	Horiz.	80	20.0	17.4	66	.75"	1	926	62.7	32	71.1	Yes	Yes
7.5	5	HV05	208-230 1Ph 200-230/460/575 3Ph	Tank	Horiz.	80	30.5	21.5	66	.75"	1	941	62.7	32	71.1	Yes	Yes
10	7	HV07	200-230/460/575 3Ph	Tank	Horiz.	80	36.6	29.4	67	.75"	1	971	62.7	32	71.1	Yes	Yes
10	7	HV07RS	460 3Ph	Tank	Horiz.	80	37.1 @ 115 PSIG	34.8	67	.75"	1	987	62.7	32	71.1	Yes	Yes

\*120 gallon tank optional



[www.hydrovaneproducts.com](http://www.hydrovaneproducts.com)

[www.hydrovaneproducts.com/contact.asp](http://www.hydrovaneproducts.com/contact.asp)  
866-615-6241

hydrovane USA  
1301 North Euclid Avenue  
Princeton, IL 61356  
United States of America



Please recycle after use.

©2014 Gardner Denver, Inc. Printed in U.S.A.  
HY-HV-HYPAC 1st Ed. 9/14

