


UPGRADE FOR NEW & EXISTING LIQUID RING COMPRESSORS

GARO® Forced Lubrication Kit

Improve the lubrication of your unit thanks to the specially designed GARO Forced Lubrication Kit. This innovative oil circulation system provides continuous lubrication and cooling to the bearings while they are in operation.

As self-contained system, the Forced Lubrication Kit delivers the required flow of clean lubricating oil at the optimum temperature and pressure to the bearings.

- Improves Unit Reliability and Efficiency
- Extends Bearing Life Expectancy
- Reduces Oil Consumption
- Enhances Heat Balancing and Mitigation of "Hotspots"
- Applicable for New Compressors and Existing Installations





Via Pompei, 15 20052 Monza MB Italy +39 039 839601

www.GDGaro.com

©2018 Garo GDG-ENHANCEDBB-1160 1st Ed. 02/18



Please recycle after use.