

D5-D30 ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR	SCFM		DRIVE CONFIG.	MOTOR RPM	MOUNT	TANK SIZE	DIMENSIONS L x W x H	WEIGHT LBS.	SOUND DBA	CONTROLLER	VOLTAGE 60 HZ	
	HP	120 PSI	145 PSI				GAL	INCHES				SINGLE PHASE	THREE PHASE
D5	5	N/A	16	BELT	1740	AS	60 GAL	52 x 23 x 44	505	65	CSC15	230	N/A
D6		N/A	18			BASE	N/A	34 x 21 x 25	378	65	CSC50	230	200/230 /460
D7.5	7.5	N/A	27			AS	80 GAL	66 x 21 x 46	665	63			
						BASE	N/A	34 x 21 x 25	404	68			
D10	10	N/A	39		1760	AS	80 GAL	66 x 21 x 46	715	66			
						BASE	N/A	41 x 27 x 37	560	65			
D15	15	N/A	57		3450	AS	120 GAL	77 x 27 x 63	970	69			
						BASE	N/A	41 x 27 x 37	600				
D20	20	87	83		3510	AS	120 GAL	77 x 27 x 63	1175	67	N/A		
						BASE	N/A	52 x 28 x 47	1010				
D25	25	100	91	AS		120 GAL	80 x 28 x 74	1480	68	N/A			
				BASE		N/A	52 x 28 x 47	1010					
D30	30	116	106	AS		120 GAL	80 x 28 x 74	1480	69	N/A			
				BASE		N/A	52 x 28 x 47	1050					
						AS	120 GAL	80 x 28 x 74	1520				

NOTES: Air System includes Air Receiver, Pre-Filter & Refrigerated Air Dryer
AS = Air System

D40-D50 ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR HP	SCFM 110 PSI	SCFM 130 PSI	SCFM 145 PSI	SCFM 175 PSI	DRIVE CONFIG.	MOUNT	DIMENSIONS L x W x H INCHES	WEIGHT LBS.	SOUND DBA	THREE PHASE VOLTAGE 60 HZ
D40	40	183.3	165.8	138.5	137.1	GEAR	BASE	63.1 x 36.6 x 67.8	1900	74	230 / 460
D50	50	222.1	212.9	167.0	164.0	GEAR	BASE	63.1 x 36.6 x 67.8	1930	74	230 / 460

D75-D100 ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR HP	SCFM 100 PSI	SCFM 125 PSI	SCFM 145 PSI	DRIVE CONFIG.	MOUNT	DIMENSIONS L x W x H INCHES	WEIGHT LBS.	SOUND DBA	CONTROLLER	THREE PHASE VOLTAGE 60 HZ
D75	75	281	277	N/A	DIRECT	BASE	79 x 47 x 79	3360	74	CSC300	460
D100	100	451	448	N/A	DIRECT	BASE	79 x 47 x 79	3770	75	CSC300	460