

UPGRADE FOR NEW & EXISTING GARO COMPRESSORS & PUMPS

GARO® Tool Kits

Assembly/Disassembly Tool Kit

This tool is used for compressor assembly and disassembly in a more accurate way.

Lining Tools (Motor Adapter Kit)

Accurate machine adjustment is an essential element of any alignment process. Single slot pre-cut shims are available in five different dimensions and in ten different thicknesses.

Fastener, Nut & Seal Kit

Complete set of bolts and nuts with toolbox.

- Improved Ease of Maintenance Applicable to GARO Units
- Mitigates the Risk of Incorrect Disassembly and Compressor Damage
- Reduced Assembly / Disassembly Time
- Consolidated Dedicated Kit Consisting of All Required Tools
- Provides the Right Quantities and Sizes Required for Each Unit (FNS Kit)
- Prevents the Wrong C-Parts Utilization (FNS Kit)
- Reduction in Unit Repair Times (FNS Kit)

 Ensure the Compressor Retains the Correct Pressures (FNS Kit)



Assembly/Disassembly Tool Kit



Lining Tools



Fastener, Nut & Seal Kit



Via Pompei, 15 20052 Monza MB Italy +39 039 839601

www.GDGaro.com

©2018 Garo GDG-ENHANCEDBB-1160 1st Ed.



Please recycle after use.