

Petroleum Pumps:

Bio-diesel

Fuel Oil

Kerosene

Aviation Gasoline

Diesel

Jet A / JP-8

Gasoline

Ethanol

E 85







MP Pumps PG, PO & PE Series Self Priming Pumps And SG, SO & SE End Suction Centrifugal Pumps Are Specifically Designed For The Transfer Of Petroleum Based Fluids.

MP Pump's Petroleum pumps capitalize on the need for pumps to handle all those fossil and bio-fuels that keep the economies of the world growing. MP Pump's Petroleum Series is targeted at the bulk transfer market and designed for use in agricultural, fuel transport, aviation and many other fuel transfer applications.

Other pump manufacturers design their pumps to be capable of handling all petroleum base fluids. This "one-pump-fits-all" approach creates unnecessary costs for most customers. MP Pumps grouped various petroleum fluids according to their characteristics and designed three distinct pump series to address those characteristics.

PO and SO Series pumps are made to handle diesel fuel, biodiesel, and fuel oil. PG and SG Series pumps are intended for use with kerosene, jet fuel A/B, and gasoline. PE and SE Series pumps match with ethanol and E85. In each case the volutes or housings, flanges, impellers, adapters, and seals are engineered for safety, performance, and durability. Pumps can also be customized to meet a customer's unique requirements. "P" pumps employ the self-priming features of MP Pumps' innovative FLOMAX® line. "S" pumps offer end-suction design.

PETROLMAXX

PO Series / SO Series

Cast Iron is the standard material for the volutes or housings, flanges, adapter and impeller. The self primer COMPATIBLE FOR DIESEL BIO-DIESEL & FUEL OIL WITH TEFC MOTOR

(PO) series is equipped with a steel wear plate. The straight centrifugal series is offered with flanged porting. As an optional material for the volute, ductile iron can be considered. The standard self-lubricated type 21 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is Ni-Resist. Electric motors are available in C Face, TEFC.

PG Series / SG Series

Ductile Iron is the standard material for the volutes or housings, flanges, and adapter. The self primer (PG) COMPATIBLE FOR KEROSENE JET A/8 & GASOLINE WITH EXPLOSION PROOF MOTOR CLASS 1 GROUP D

series is equipped with an aluminum wear plate. The straight centrifugal series is offered with flanged porting. The standard open impeller material for the self-priming series (PG) is cast iron with aluminum as an option. The standard enclosed impeller material for the straight centrifugal series is aluminum. The standard self-lubricated type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is silicon carbide. Electric motors are available in C Face, explosion proof Class 1 group D.

PE Series / SE Series

Ductile Iron is the standard material for the volutes or housings, flanges, and adapter with a steel wear plate COMPATIBLE FOR ETHANOL, & EBS WITH EXPLOSION PROOF MOTOR CLASS 1

for the self primer series (PE). The standard impeller material is cast iron with 316 stainless steel as an option for the PE series. The straight centrifugal series is offered with flanged porting. The standard self lubricated type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is silicon carbide. Electric motors are available in C Face, explosion proof Class 1 Group D.


MP Pumps has specifically reengineered its popular Flomax® Self-Priming Series for compatibility with clean, non-abrasive petroleum products.

Transfer and delivery of various fuels such as gasoline, ethanol, biodiesel, and fuel oils are just a few of the petroleum based products the Flomax® Series is suitable for handling.

Long recognized as the leader in self-priming applications, the Flomax® Series addresses today's fuel market by offering:

- Five (5) performance models.
- Various drive options.
- Specific mechanical seal offerings.
- Materials of construction compatible for three (3) distinct fuel classifications.

By classifying various fuels into three (3) distinct segments, MP Pumps can recommend that its design is capable of handling the specific fuel groups without incurring the additional cost associated with "one pump for all fuels".



MP Pumps, Inc. Phone: (800) 563-8006 FAX: (586) 293-8469 www.mppumps.com

2

Model PG Pumps Compatible For Gasoline, Kerosene, Avgas & Jet Fuel



The "PG" model is available in Pedestal mount for flexible coupling or Close Coupled mount to C Face Class I Group D Explosion Proof electric motors. Ductile Iron is the standard construction for the volute and adapter. The open impeller is standard in cast iron construction with aluminum as an optional material. Standard material for the wear plate is aluminum. The standard self-lubricated Type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is silicon carbide.

3



				STANDARD MATERIALS OF CONSTRUCTION					. MATERIALS	
MODEL	SIZE	MOUNTING	VOLUTE	IMPELLER	WEAR PLATE	O RING/ GASKET	SEAL	VOLUTE	IMPELLER	WEAR PLATE
PG 8	2" X 2"	Explosion Proof	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	С	Aluminum	С
PG 8	2" X 2"	Pedestal	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	0 N S	Aluminum	O N S
PG 10	2" X 2"	Explosion Proof	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS		Aluminum	U L
PG 15	3" X 3"	Explosion Proof	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	T F	Aluminum	T F
PG 15	3" X 3"	Pedestal	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS		Aluminum	A C
PG 30	3" X 3"	Pedestal	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	T O R	Aluminum	T O R
PG 40	4" X 4"	Pedestal	Ductile Iron	Cast Iron	Aluminum	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	v	Aluminum	Y

Model PO Pumps Compatible For BioDiesel, Fuel Oil & Diesel



The "PO" model mounting offerings for fuel oil and diesel fuel applications include both Pedestal mount for flexible coupling and Close Coupled mount to C Face, TEFC electric motors. Cast Iron is the standard construction for the volute, adapter and open impeller. Standard material for the wear plate is steel. The volute is also available in ductile iron. The standard self-lubricated Type 21 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is Ni-Resist.



				STANDARD N	MATERIALS	OPTIONAL	MATERIALS			
MODEL	SIZE	MOUNTING	VOLUTE	IMPELLER	WEAR PLATE	O RING/ GASKET	SEAL	VOLUTE	IMPELLER	WEAR PLATE
PO 8	2" X 2"	TEFC	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	С	С
PO 8	2" X 2"	Pedestal	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	O N S	O N S
PO 10	2" X 2"	TEFC	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	U L	U L
PO 15	3" X 3"	TEFC	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	T F	T F
PO 15	3" X 3"	Pedestal	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	A C	A C
PO 30	3" X 3"	Pedestal	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	T O R	T O R
PO 40	4" X 4"	Pedestal	Cast Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 21 Viton/Carbon/ NiResist/SS	Ductile Iron	Y	Y

Model PE Pumps Compatible For Ethanol & E 85





The "PE" model is available in Pedestal mount for flexible coupling or Close Coupled mount to C Face Class I Group D Explosion Proof electric motors. Ductile Iron is the standard construction for the volute and adapter. The open impeller is standard in cast iron construction with 316 SS as an optional material. Standard material for the wear plate is steel. The standard self-lubricated Type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is silicon carbide.

5



				STANDARD N	MATERIALS	OPTIONAL	MATERIALS			
MODEL	SIZE	MOUNTING	VOLUTE	IMPELLER	WEAR PLATE	O RING/ GASKET	SEAL	VOLUTE	IMPELLER	WEAR PLATE
PE 8	2" X 2"	Explosion Proof	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	C	316 SS	С
PE 8	2" X 2"	Pedestal	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	O N S	316 SS	O N S
PE 10	2" X 2"	Explosion Proof	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	U L	316 SS	U L
PE 15	3" X 3"	Explosion Proof	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	T F	316 SS	T F
PE 15	3" X 3"	Pedestal	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	A C	316 SS	A C
PE 30	3" X 3"	Pedestal	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	T O R	316 SS	T O R
PE 40	4" X 4"	Pedesta	Ductile Iron	Cast Iron	Steel	Viton Cork/Nitrile	Type 2 Viton/Carbon/ Sil.Car./SS	Y	316 SS	Y






MP Pumps, Inc. Phone: (800) 563-8006 FAX: (586) 293-8469 www.mppumps.com

6

MP Pumps has adapted its Petroleum End Suction series pumps specifically for use with clean, non-abrasive petroleum products.

Transfer and delivery of various fuels such as gasoline, ethanol, biodiesel, and fuel oils are just a few of the petroleum based products the end suction series is capable of handling. The Petroleum End Suction Series offers:

- Six (6) performance models.
- Enclosed impellers.
- Specific mechanical seal offerings.
- Flat flange ports.
- Materials of construction compatible for three (3) distinct fuel classifications.



- TYPE 21 VITON/CARBON/NIRESIST/SS
- TYPE 2 VITON/CARBON/SILICON CARBIDE/SS

MOUNTING OPTIONS

- PEDESTAL
- CLOSE CPLD. AND PUMPAK (SHOWN)
- EXPLOSION PROOF CLASS I GROUP D

Model SG Pumps Compatible For Gasoline, Kerosene, Avgas & Jet Fuel



The "SG" models are available in Pedestal mount for flexible coupling or Close Coupled mount to C-Face Class 1 Group D Explosion Proof motors. Ductile Iron is the standard construction for the housing and adapter. Aluminum enclosed impellers are standard in the SG Series. The standard self-lubricating Type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and SS spring. The stationary seal face is silicon carbide.



8

				STANDARD MATERIALS OF CONSTRUCTION				
MODEL	SIZE	PORT	MOUNTING	HOUSING	IMPELLER	GASKET	SEAL	
SG60	1-1/4" x 1"	NPT	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG80	1-1/2" x 1-1/4"	Flange	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG80	1-1/2" x 1-1/4"	Flange	Pedestal	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG120	2" x 1-1/2"	Flange	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG120	2" x 1-1/2"	Flange	Pedestal	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG180	3" x 1-1/2"	Flange	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG180	3" x 1-1/2"	Flange	Pedestal	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG300	3" x 2-1/2"	Flange	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG300	3" x 2-1/2"	Flange	Pedestal	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG700	4" x 3"	Flange	Explosion Proof	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SG700	4" x 3"	Flange	Pedestal	Ductile Iron	Aluminum	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	

Model SO Pumps Compatible For BioDiesel, Fuel Oil & Diesel



The "SO" mounting offerings for fuel oil and diesel fuel applications include both Pedestal mount for flexible coupling and Close Coupled mount to NEMA C-Face, TEFC electric motors. Ductile Iron is the standard construction for the housing, and Cast Iron is the standard construction for the adapter and enclosed impeller. The standard self-lubricating Type 21 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is Ni-Resist.

9



				STANDARD MATERIALS OF CONSTRUCTION				
MODEL	SIZE	PORT	MOUNTING	HOUSING	IMPELLER	GASKET	SEAL	
SO60	1-1/4" x 1"	NPT	TEFC	Cast Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO80	1-1/2" x 1-1/4"	Flange	TEFC	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO80	1-1/2" x 1-1/4"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO120	2" x 1-1/2"	Flange	TEFC	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO120	2" x 1-1/2"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO180	3" x 1-1/2"	Flange	TEFC	Ductile Iron	Ductile Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO180	3" x 1-1/2"	Flange	Pedestal	Ductile Iron	Ductile Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO300	3" x 2-1/2"	Flange	TEFC	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO300	3" x 2-1/2"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO700	4" x 3"	Flange	TEFC	Ductile Iron	Ductile Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	
SO700	4" x 3"	Flange	Pedestal	Ductile Iron	Ductile Iron	Fiber	Type 21 Vit/Carbon/NiResist/SS	




The "SE" models are available in Pedestal mount for flexible coupling or Close Coupling to NEMA C-Face Class 1 Group D Explosion Proof motors. Ductile iron is the standard construction for the housing and adapter. The enclosed impeller is standard in cast iron construction. The standard self-lubricating Type 2 mechanical seal is equipped with a carbon rotating face, viton elastomer and stainless steel spring. The stationary face is silicon carbide.



10

				STANDARD MATERIALS OF CONSTRUCTION				
MODEL	SIZE	PORT	MOUNTING	HOUSING	IMPELLER	GASKET	SEAL	
SE60	1-1/4" x 1"	NPT	Explosion Proof	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE80	1-1/2" x 1-1/4"	Flange	Explosion Proof	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE80	1-1/2" x 1-1/4"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE120	2" x 1-1/2"	Flange	Explosion Proof	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE120	2" x 1-1/2"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE180	3" x 1-1/2"	Flange	Explosion Proof	Ductile Iron	Ductile Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE180	3" x 1-1/2"	Flange	Pedestal	Ductile Iron	Ductile Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE300	3" x 2-1/2"	Flange	Explosion Proof	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE300	3" x 2-1/2"	Flange	Pedestal	Ductile Iron	Cast Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE700	4" x 3"	Flange	Explosion Proof	Ductile Iron	Ductile Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	
SE700	4" x 3"	Flange	Pedestal	Ductile Iron	Ductile Iron	Fiber	Type 2 Vit/Carbon/Sil. Car./SS	

Petroleum End Suction 3500 RPM



We don't just go with the flow, we create it!™

For more information on MP Pumps, Inc. and our products, visit www.mppumps.com.

