

Gardner Denver

1.5-8 HP | GAS & ELECTRIC RECIPROCATING AIR COMPRESSORS

Air-On-Demand





Solid Construction Exceptional Performance

A Winning Combination

Gardner Denver compressors are proven units, known for their reliability over decades of use. We know our products and understand how they operate in many different operating environments. No matter the application, Gardner Denver gets the job done.

Your Business is Our Business


What is your line of work? Construction? Industrial?

For almost a century, Gardner Denver has been designing and manufacturing one of the best compressors available. Gardner Denver offers a complete line of portable compressors— with solid construction and exceptional performance— to put your mind at ease.



The Air-On-Demand Advantage

- 1.5-8 HP Range
- 100-175 PSIG
- 4.3-15.7 CFM
- Hand-Held, Wheeled, Base Mounted
- Electric & Gas
- Splash Lubricated



It's All in the Details

Portable Compressors

- 120 Volt Single Phase, 60 Hz Motors with 15 Amp Plug
- Industrial Honda OHV Engines
- Factory Filled with Heavy Duty Lubricants
- Fully Enclosed Belt Guard (where applicable)
- Industrial Grade Semi Pneumatic Tires (where applicable)
- Pressure Gauges
- Lift Handles with Rubber Grips
- Quick Connect Fitting
- Belt Tightener (where applicable)
- Auto Start/Stop on Electric Models
- Idle Control for Added Safety (Gas Models)
- Quality Pilot Valve (Gas Models)





PORTABLE AIR COMPRESSORS

UNIT MODEL	HP	POWER	LUBRICATION	COMPRESSOR PUMP	STAGES	TANK GALLONS	CFM DELIVERY		WT LBS
							100 PSI	175 PSI	
6226	2	Electric	Splash Lubricated	Cast Iron	Single	5 Gal. Twin Stack	5.9	N/A	57
6202	1.5	Electric	Splash Lubricated	Cast Iron	Single	20 Gal. Horizontal	5.9	N/A	170
6205	1.5	Electric	Splash Lubricated	Cast Iron	Single	8 Gal. Twin	5.9	N/A	160
6204	5.5	Honda OHV	Splash Lubricated	Cast Iron	Single	20 Gal. Horizontal	9.0	N/A	177
6207	5.5	Honda OHV	Splash Lubricated	Cast Iron	Single	8 Gal. Twin	9.0	N/A	170
6229	8	Honda OHV	Splash Lubricated	Cast Iron	Two	8 Gal. Twin	N/A	15.7	265

Note: Gardner Denver recommends that the electrical units do not exceed six starts per hour. Units are not CSA approved.

Sales & Service **Distributors** Across America

An Extensive Network

By leveraging the extensive network of Gardner Denver factory-trained authorized local distributors, your sales, service and technical support needs can be handled quickly and easily.



To find a distributor visit:
gardnerdenver.com/gdproducts

The leader in every market we serve
by continuously improving all business processes
with a focus on innovation and velocity

**Gardner
Denver**[®]


Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenver.com/gdproducts



©2017 Gardner Denver, Inc. Printed in U.S.A.
GR-AOD 1st Ed. 6/17
Supersedes GR-AOD-102 2nd Ed. 11/12

 Please recycle after use.