

**COMPRESSOR DATA SHEET**



**In Accordance With Federal Uniform Test Method for Certain Lubricated Air Compressors**

**Rotary Compressor: Variable Frequency Drive**

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: <b>Gardner Denver</b>			
2	Model Number: <b>ETSV150-200hp-200psi</b>	Date:	<b>02/07/24</b>	
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled	Type:	<b>Screw</b>	
		# of Stages:	<b>1</b>	
3*	Full Load Operating Pressure <sup>b</sup>	<b>200</b>	psig <sup>b</sup>	
4	Drive Motor Nominal Rating	<b>200</b>	hp	
5	Drive Motor Nominal Efficiency	<b>95.5</b>	percent	
6	Fan Motor Nominal Rating (if applicable)	<b>7.5</b>	hp	
7	Fan Motor Nominal Efficiency	<b>86.5</b>	percent	
8*	Input Power (kW)		Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	188.04		<b>833.6</b>	<b>22.56</b>
	158.92		<b>708.6</b>	<b>22.43</b>
	133.12		<b>579.6</b>	<b>22.97</b>
	107.28		<b>449.5</b>	<b>23.87</b>
	99.97		<b>412.1</b>	<b>24.26</b>
	92.65		<b>374.6</b>	<b>24.73</b>
9*	Total Package Input Power at Zero Flow <sup>c, d</sup>	<b>24.7</b>	<b>kW</b>	
10	Isentropic Efficiency	<b>81.72</b>	<b>%</b>	
11	<p align="center"><b>Note: Graph is only a visual representation of the data in Section 8</b>                      Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35                      X-Axis Scale, 0 to 25% over maximum capacity</p>			

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator

Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:  
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	NO Load / Zero Flow Power
<u>m<sup>3</sup> / min</u>	<u>ft<sup>3</sup> / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.1