

COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: Gardner Denver			
2	Model Number: Ultima U75-145psi		Date:	05/11/21
	<input checked="" type="checkbox"/> Air-cooled	<input type="checkbox"/> Water-cooled	Type:	Screw
	<input type="checkbox"/> Lubricated	<input checked="" type="checkbox"/> Oil Free	# of Stages:	2
3*	Full Load Operating Pressure ^b	145		psig ^b
4	Drive Motor Nominal Rating	50		hp
5	Drive Motor Nominal Efficiency	97.0		percent
6	Fan Motor Nominal Rating (if applicable)	0.78, 2X 3.75		hp
7	Fan Motor Nominal Efficiency	87.9		percent
8*	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	84.38		348.7	24.20
	81.87		333.3	24.56
	79.38		318.0	24.97
	76.93		302.6	25.42
	74.51		287.2	25.94
	72.12		271.9	26.53
9*	Total Package Input Power at Zero Flow ^{c, d}		8.4	kW
10	<p align="center">Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</p>			

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator
 Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
<u>m³ / min</u>	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2