

# **SERIES 30**

# 1" x 3/4" End Suction Centrifugal Pump

SERIES 30 end suction centrifugal pumps are close-coupled to standard NEMA "C" face motors. All models are available in cast iron, bronze or aluminum construction to suit a wide variety of liquids.

All fasteners are stainless steel to reduce corrosion. Impellers are dynamically balanced to improve efficiency and bearing life.

Standard carbon / ceramic / Viton mechanical seal is self-adjusting and corrosion resistant to handle almost any liquid.

Completely tested "Wet End" PumPAKs are available without motors. The MP PumPAK® can be mounted to standard NEMA C frame motors in just minutes.



#### **Application**

- Agricultural
- Commercial
- Industrial
- OEM

# **SPECIFICATIONS:**

Suction And Discharge 1" x 3/4" NPT

Materials Of Construction Bronze, Cast iron

Flow Up to 45 GPM

Head Feet Up to 40'

Impeller 3.25" semi-open cast iron, bronze

Motor Up to 3/4 HP

Drive Options Close coupled 56C, Hydraulic motor .37

cu. in., Hydraulic motor .45 cu. in.,

PumPAK® (without motor)

Seal Special seal material combinations

available (consult factory), Standard


carbon / ceramic / Viton


Max Solid Size .27"


#### **CUBIC METERS PER HOUR** 0 5 10 MODEL SERIES 30 3.25 DIA SIZE 1 X 3/4 40 **SPEED** 3500 RPM 3.12 35 2.88 35 10 30 TOTAL HEAD - FEET TOTAL HEAD - METERS 2.50 25 20 75 HP 15 10 33 HP 10 15 20 35 0 5 25 30 40 45 50 **GALLONS PER MINUTE**



#### SERIES 30 3.25 Impeller







### MP PUMPS SERVICE PARTS LIST


Straight Centrifugal

Pumpak

Electric Motor Drive

Mechanical Seal

Series 30 1" x ¾" Pipe Size



IMPORTANT: When ordering parts, specify model and serial number shown on nameplate. N/S means "not shown" in exploded view of parts.

		DESCRIPTION	QUANTITY REQUIRED PER MODEL				
			ROTATION PIPE SIZE	ALL MODELS LISTED ARE RIGHT HAND ALL MODELS LISTED ARE 1" x 3/4"			
							ITEM
NO.			PART NO.	MODEL NO.	23221 23222 24319 22678	25 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5	23220 23938 24318 24186
HOUSIN	IG						
	22915	Housing Assembly - Inc:		1			
3		Housing - Cast Iron		1			
4	28059	Stud - S.S 5/16"	4				
6	21255	Pipe Plug - S.S 1/8" NPT	2				
	NA	Housing Assembly - Inc:			1		
3		Housing - Aluminum			1		
4	28059	Stud - S.S 5/16"			4		
6	21255	Pipe Plug - S.S 1/8" NPT					
	22914	Housing Assembly - Inc:				1	
3 4		Housing - Bronze				1	
4	21150	Stud - Br 5/16"				4	
6	21185	Pipe Plug - Bronze - 1/8" NPT				1	



**FORM 7020-E** 

PRINTED IN U.S.A. (8-97)




			QUANTITY REQUIRED PER MODEL			
			ROTATION	ALL MODELS LISTED ARE RIGHT HAN		
ITEM			PIPE SIZE METAL MODEL NO.	ALL MODELS LISTED ARE 1" x 3/4"  CAST IRON   ALUMINUM   BRONZI		
NO.	PART NO.	DESCRIPTION		23221 23222 24319 22678	NA NA NA NA NA	23220 23938 24318 24186
HOUSING	i					
17	21244	Hex Nut - S.S 5/16"		4	4	
19	21238	Lockwasher - S.S 5/16"		4	4	
17	21179	Hex Nut - Br 5/16"				4
19	19 21184 Washer - Br. 5/8"					4
1	21126	Gasket		4	4	4
MPELLER						
10	22573	Impeller C.I 3-1/4" dia. for Model 23221		1		
10	NA	Impeller - Alum 3-1/4" dia, for Model 23219			1	
10	22572	Impeller - Br 3-1/4" dia. for Model 23220				1
10	22138	Impeller - C.I 2-7/8" dia. for Model 23222		1		
10	NA	Impeller - Alum 2-7/8" dia. for Model 24316			1	
10	22137	Impeller - Br 2-7/8" dia. for Model 23938				1
10	22149	Impeller - C.I 3-1/8" dia. for Model 24319		1		
10	NA	Impeller - Allum 3-1/8" dia. for Model 24317			1	
10	22148	Impeller - Br 3-1/8" dia. for Model 24318				1
10	22143	Impeller - C.I 2-1/2" dia. for Model 22678		1		
10	NA	Impeller - Alum 2-1/2" dia. for Model 24320			1	
10	22142	Impeller - Br. 2-1/2" dia. for Model 24186				1
15	22131	Impeller Drive Sleeve 5/8"		1	1	1
9	22588	Lock Nut - S.S 3/8"		1	1	1
2	21865	Impeller Drive Key		1	1	1
Clamp		9				
	23002	Clamp Assembly Inc.				
8		Clamp		2	2	2
5	21284	Hex Nut - S.S 5/16"		2	2	2
18	21238	Lockwasher - S.S 5/16"		2	2	2
16	21264	Capscrew - S.S 5/16*		2	2	2
SEAL						
7	22272	Seal Assembly		1	1	1
11	22133	Seal Spring Retainer		i	i	i
ADAPTOR		Advates Continue		1/328		
14 14	22130	Adaptor - Cast Iron		1		
14	<b>NA</b> 22129	Adopter - Aluminum Adapter - Bronze			1	
	22123	Adaptor - Brotize				1
12	21251	Capscrew - S.S 3/8"		4	4	4
13	21266	Lockwasher - S.S 3/8"		4	4	4



# **FORM 7020-E**

PRINTED IN U.S.A. (8-97)





	ITEM NO.	PART NO.	DESCRIPTION	QTY.
_	1	21185	PIPE PLUG B - 1/8" NPT	2
	2	21107	HOUSING D - 1" X 3/4"	1
	3	22588	LOCK NUT S.S 3/8"-24	1
	4	31224	LOCK WASHER S.S SELF LOCKING	1
	5	22573	IMPELLER C - Ø3.25	1
	6	31103	WASHER S.S.	1
*	7	22272	SEAL ASSEMBLY T-2100 - VITON	1
*	8	21126	GASKET - NI-2085	1
	9	21865	KEY S.S WOODRUFF #2	1
	10	22131	DRIVE SLEEVE	1
	11	23002	CLAMP ASSY. S.S 5/8 & 3/4	1
	12	21251	HEX HD SCREW S.S 5/16"-18 X .88"	4
	13	21266	LOCKWASHER S.S 3/8"	4
	14	28059	STUD S.S 5/16 118 X 1.19"	4
	15	22163	LOCK WASHER S.S 5/16 X 1/8	6
	16	21284	HEX NUT- 5/16"-18	6
	17	22130	ADAPTOR- CAST IRON	1

<sup>\*-</sup> RECOMMENDED REPLACEMENT PARTS

