

CERTIFIED Service & Support

FOR NASH® AND HOFFMAN® & LAMSON® PRODUCTS

The 50,000 square-foot Gardner Denver Nash facility in Moody, Alabama offers a full range of service and support for NASH and Hoffman & Lamson products as well as other brands of liquid ring vacuum pumps, compressors and centrifugal blowers.

Staffed by an experienced team of factory trained technicians, CNC machinists, manufacturing engineers and support professionals, the service center provides expert level repairs to restore performance and return your unit to service and quickly as possible.

Restore performance and efficiency, maintain reliability and lower total cost of ownership with OEM quality parts, factory trained technicians, and over a century of engineering, design and manufacturing expertise.

NASH OPERATIONS & SERVICE CENTER MOODY, ALABAMA

Ph: 205 702 6323 | nash@gardnerdenver.com

CERTIFIED SERVICE & SUPPORT FOR:

- NASH PUMPS & COMPRESSORS, all sizes and models
- HOFFMAN & LAMSON BLOWERS

SPECIALIZED EQUIPMENT

- CNC Vertical Turning Center & CNC Horizontal Boring Mill
- 1250 HP, 600 HP, & 250 HP Test Motors
- Computerized Horizontal Balance Machine
- Sandblasting & Paint Booths
- (2) CNC Horizontal Lathes & Vertical Lathes
- (5) 20 Ton Cranes & (3) 10 Ton Cranes

FULL INVENTORY OF OEM PARTS, EXCHANGE AND REMANUFACTURED PUMPS IN STOCK



NASH OPERATIONS & SERVICE CENTER MOODY, ALABAMA

2150 A.E. Moore Road | Moody, AL 35004

Ph: 205 702 6323

1-800-770-NASH (6274)

nash@gardnerdenver.com

- Complete repair and refurbishment to factory standards
- OEM Parts, Design Drawings & Specifications
- Inventory of OEM Parts, Exchange Pumps & Remanufactured Units
- Failure analysis, inspection and disassembly reports
- Performance, Capacity, and ASME Testing
- Fiberscope Inspections and Vibration Analysis
- Specialized Coating and Paints
- Static & Dynamic Balancing



Demanding industrial processes require equipment that can stand up to the task, but even the most durable equipment requires routine maintenance and occasional service and repair to maintain reliable and efficient performance.

When you need service you need it fast - and you need it to last. Don't risk it with generic parts, unexperienced repair shops, and untrained technicians.

Our certified team of factory trained technicians, certified service centers, and available inventory of OEM parts deliver quality, long lasting repairs lowering your total cost of ownership and returning unit to service as quickly as possible.

Some companies claim to offer service for Nash Products, but only we certify it.

Protect your investment. Insist on OEM parts and CERTIFIED service for your NASH and HOFFMAN & LAMSON equipment.

Our level of service is unparalleled. Our pricing is competitive. And performance is GUARANTEED.



Gardner Denver Nash, LLC

PO Box 130 Bentleyville, PA 15314 USA 800-553-NASH +1 724 239 1500

nash@gardnerdenver.com www.GDNash.com

©2017 Gardner Denver Nash, LLC Printed in U.S.A. AM-MOODY-1145-0717 1st Ed. 12/17





LIQUID RING PUMP & COMPRESSOR SERVICES & CAPABILITIES

- Pump/Compressor Repair and Remanufacturing
- Fiberscope Inspections
- Capacity and Performance Testing
- Vibration Analysis
- Static and Dynamic Balancing
- Shaft Metalizing
- Cladding
- Welding
- Unit Exchanges Pumps in Stock
- CNC Machining
- Sandblasting
- Painting & Coatings
- Failure Analysis
- Inspection and Disassembly reporting
- NASH CERTIFIED Guarantee

CENTRIFUGAL BLOWER SERVICES & CAPABILITIES

- Blower Repair and Remanufacturing
- ASME Blower Testing
- Mechanical Blower Testing
- Vibration Analysis
- Static and Dynamic Balancing
- Welding
- CNC Machining
- Sandblasting
- Painting
- Disassembly Reporting
- HOFFMAN & LAMSON CERTIFIED Guarantee



