


L04-L29 (5-40 HP) FIXED-SPEED ROTARY SCREW COMPRESSORS

## L-Series



## Advanced Technology Inspired Simplicity

### A Better Approach

Champion has a long history of manufacturing compressed air equipment. With our L-Series line of products, we have uniquely combined simplicity with cutting edge design. The result—a compressor that delivers outstanding performance with unprecedented serviceability.

### The Total Package

Champion has the total package—extensive compressor and air treatment product lines, sales and service support through our extensive network of authorized local distributors, and industry leading warranty programs. Because we offer more than just compressed air equipment, we can provide solutions that keep you running, protect your production objectives, and save you money.



Without sacrificing serviceability, the L-Series compressor packages feature some of the smallest footprints in the industry.








## Compact, Quiet Compressors

### Nearly Silent Noise Levels




5

## Stay Focused on What Is Important

Compressors are more than just a financial investment. They are a key component in ensuring that you, as a manufacturer, processor and operator, receive consistent, high-quality low-cost air. Champion uses the latest design techniques to develop a compressor that focuses on the three most important aspects of a compressor.

### Reliability. Performance. Value.



## Direct Gear Drive Fewer Hose Connections Direct Angle Integrated Air Filter

Integrated Thermostatic Mixing Valve

Injection Low Rotational Speeds

## RELIABILITY

Integrated Oil Filter Integrated Oil Separator

**Belt Drive** 

Reduced Number Fully Integrated Airend of Components Semi Integrated Airend

Fail Safe Shaft System Less Leak Opportunities



## Get in Touch with the Next Generation of Compressor Controllers

#### State-of-the-Art

Champion completes it's industry leading compressor packages with the state-of-the-art dual position Pilot controller and the full color Governor™ touchscreen controller. Featuring advanced software and an easy to use interface, the Pilot controller provides and displays an extensive amount of data on the operation of your compressor. The cutting edge graphics on the Governor™ provide necessary compressor data and full color schematics in seconds.




#### Governor™ Touchscreen Controller Features

- Available on L23-L29 compressor models
- User-friendly navigation with state-of-the-art graphics and design
- Machine status available on a 4.3-inch display
- Detailed schematics at your fingertips
- Advanced machine diagnostics
- Data logging and iConn connection
- Web server to allow access to the Governor<sup>™</sup> from your desktop

#### Pilot Controller Features

- Available on L04-L22 compressor models
- Real time clock
- Second pressure setting
- Discharge/line/network pressure data displayed
- Advanced fault history log
- Programmable inputs and outputs
- RS485-Modbus RTU standard




## Keeping the System Healthy

### **Total System Protection**

For decades Champion has been supporting the compressed air industry with high quality, long-lasting compressor and air treatment solutions. Carrying on that legacy, our robust line of parts, lubricant and downstream accessories ensure your system stays healthy.

The focus on total system protection by Champion not only includes OEM parts and fluid solutions, but a commitment to the longevity of your equipment through our industry leading warranty programs.

# your equipment through our industry leading warranty programs. Protect your investment.





## Sales & Service Distributors Across America

#### An Extensive Network

Your sales, service and technical support needs will be handled quickly and easily by our extensive network of Champion factory-trained, authorized local distributors. Maintaining and adequately servicing your compressor has never been easier.



#### LO4-L29 ROTARY SCREW COMPRESSOR

MODEL	DE	DRIVE MOTOR		50 HZ				60 HZ							
				NOMINAL PRESSURE		FAD¹		NOMINAL PRESSURE		FAD¹		WEIGHT		DIMENSIONS L × W × H	
	HP	KW	PSIG	BAR	ACFM	M³/MIN	PSIG	BAR	ACFM	M³/MIN	DB(A)	LBS	KG	IN. (MM)	
L04	5	4	NA	NA	NA	NA	100 125 190	6.9 8.6 13.0	19.4 18.2 12.9	0.55 0.52 0.36	68	373	169	27 × 25 × 41 (686 × 635 × 1041)	
L05	7.5	5	NA	NA	NA	NA	100 125 190	6.9 8.6 13.0	28.4 24.9 18.3	0.8 0.71 0.52					
L07	10	7	110 145 190	7.5 10.0 13.0	45.9 37.4 30.0	1.30 1.06 0.85	100 125 190	6.9 8.6 13.0	44.5 38.7 26.4	1.26 1.10 0.75	71	452	205	_ 27 × 25 × 41 (686 × 635 × 1041)	
L11	15	11	110 145 190	7.5 10.0 13.0	66.0 56.8 46.6	1.87 1.61 1.32	100 125 190	6.9 8.6 13.0	63.1 57.9 44.1	1.79 1.64 1.25		483	219		
L15	20	15	110 145 190	7.5 10.0 13.0	95.3 79.8 63.5	2.70 2.26 1.80	100 125 190	6.9 8.6 13.0	89.4 83.4 63.1	2.53 2.36 1.79	73	739	335		
L18	25	18	110 145 190	7.5 10.0 13.0	114.7 96.7 82.6	3.25 2.74 2.34	100 125 190	6.9 8.6 13.0	110.9 101.9 80.2	3.14 2.89 2.27	74	796	361	31 × 28 × 47 (787 × 711 × 1194)	
L22	30	22	110 145 190	7.5 10.0 13.0	128.8 113.3 92.1	3.65 3.21 2.61	100 125 190	6.9 8.6 13.0	125.8 116.5 92.0	3.56 3.30 2.61		810	367		
L23	30	22	110 145 190	7.5 10.0 13.0	146.9 121.8 105.2	4.16 3.45 2.98	100 125 190	7.5 10 13	148.7 125.0 100.6	4.21 3.54 2.85	68	1433 650	650		
L26	35	26	110 145 190	7.5 10.0 13.0	170.9 145.8 121.5	4.84 4.13 3.44	100 125 190	7.5 10 13	172.8 148.1 125.7	4.89 4.19 3.56		1493	1493 677		
L29	40	30	110 145 190	7.5 10.0 13.0	194.9 169.9 145.5	5.52 4.81 4.12	100 125 190	7.5 10 13	193.1 173.0 147.4	5.47 4.90 4.17		1501	681		

<sup>1)</sup> Data measured and stated in accordance with ISO1217, Ed. 4, Annex C & Annex E at the following conditions: Air Intake Pressure 1 bar A, Air Intake Temperature 20° C, Humidity 0% (Dry)

Over 1,100 Champion distributors ready to provide solutions to all your compressed air needs



We're Where You Need Us

<sup>2)</sup> Measured in free field conditions in accordance with ISO 2151, tolerance +/-  $3\,\mathrm{dB}$ 

The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



1301 North Euclid Avenue Princeton, Illinois 61356 USA 866-276-4330 www.ChampionPneumatic.com







©2021 Gardner Denver, Inc. Printed in U.S.A. CS-L04-L29 4th Ed. 3/21

