

SERIES 130 2" x 1-1/2" End Suction Centrifugal Pump

SERIES 130 high volume centrifugal pumps are close-coupled to standard NEMA "C" face motors. Open adaptor protects motor. All models are available in cast iron, bronze or aluminum construction to suit a wide variety of liquids.

All fasteners are stainless steel to reduce corrosion. Impellers are dynamically balanced to improve efficiency and bearing life.

Standard carbon / ceramic / Viton mechanical seal is self-adjusting and corrosion resistant to handle almost any liquid.

Completely tested "Wet End" PumPAKs are available with or without motors and can be mounted to standard "C" frame motors in just minutes.




Application

- Agricultural
- Commercial
- IndustrialOEM


SPECIFICATIONS:

| Suction And Discharge | 2" x 1-1/2" NPT |
|---------------------------|---|
| Materials Of Construction | Bronze, Cast iron |
| Flow | Up to 160 GPM |
| Head Feet | Up to 60' |
| Impeller | 4" semi-open |
| Motor | Up to 3 HP |
| Drive Options | Close coupled 56C, Hydraulic motor .37 cu. in., Close coupled 184C, Pedestal, PumPAK® (without motor) |
| Seal | Special seal material combinations available (consult factory), Standard carbon / ceramic / Viton |
| Max Solid Size | .53" |






SERIES 130







IMPORTANT: When ordering parts, specify model and serial number shown on nameplate.

| ITEM NO. | | DESCRIPTION | QUANTITY REQUIRED PER MODEL | | | |
|-------------|---------|-------------------------------|--------------------------------------|----------------|----------------|----------------|
| | | | ROTATION ALL MODELS LISTED ARE RIGHT | | | |
| | PART NO | | PIPE SIZE | 2" x 1-1/2" | 2" x 1-1/2" | 2" x 1-1/2 |
| | | | METAL | CAST IRON | ALUMINUM | BRONZE |
| | | | MODEL NOS. | 23225 | 23223 | 23224 |
| | | | | 23228 23231 | 23226 23229 | 23227 23230 |
| IOUSIN | G | | | | | |
| | 22930 | Housing Assembly - Inc. | | 1 | | |
| 3 | | Housing - Cast Iron | | 1 | | |
| 4 | 21243 | Stud - S.S 5/16" | | 6 | | |
| 6 | 21255 | Pipe Plug - S.S 1/8" NPT | | 2 | | |
| | 22928 | Housing Assembly - Inc.: | | | 1 | |
| 3 | | Housing - Aluminum | | | 1 | |
| 4 | 21243 | Stud - S.S 5/16" | | | 6 | |
| 6 | 21255 | Pipe Plug - S.S 1/8" NPT | | | 1 | |
| 17 | 21244 | Hex Nut - S.S 5/16" | | 6 | 6 | |
| 19 | 21238 | Lockwasher - S.S 5/16" | | 6 | 6 | |
| | 22929 | Housing Assembly - Inc. | | | | 1 |
| 3 | | Housing - Bronze | | | | 1 |
| 4 | 21150 | Stud - Br 5/16" | | | | 6 |
| × 6 | 21185 | Pipe Plug - Bronze - 1/8" NPT | | | | 1 |
| 17 | 21179 | Hex Nut - Br 5/16" | | | | 6 |
| 19 | 21184 | Washer - Br. | | | | 6 |
| 1 | 21149 | Gasket | | 1 | 1 | 1 |



34800 Bennett Dr. Fraser, MI 48026 (313) 293-8240 TLX: 358-238 DIVISION OF TECUMSEN PRODUCTS CO. FAX: (313) 293-8469

5

FORM 7018-B PRINTED IN U.S.A.



34800 BENNETT - FRASER, MI 48026-1686 (586) 293-8240 - FAX (586) 293-8469 (800) 563-8006 - www.mppumps.com

SERIES 130

| | | | QUANTITY REQUIRED PER MODEL | | | |
|---|----------|---|-----------------------------|-------------|----------------|-------------|
| | | | ROTATION | | S LISTED ARE R | |
| | | | PIPE SIZE | 2" x 1-1/2" | 2" x 1-1/2" | 2" x 1-1/2" |
| ITEM | PART NO. | DESCRIPTION | METAL | CAST IRON | ALUMINUM | BRONZE |
| NO. | | | MODEL NOS. | 23225 | 23223 | 23224 |
| | | | | 23228 | 23226 | 23227 |
| | L | | | 23231 | 23229 | 23230 |
| MPELLE | | | | | | |
| Mrecce 10 | 22628 | Impeller - 4" Dia C.I (Model 23231) | | 1 | | |
| 10 | 22626 | Impeller - 4" Dia, - Alum, - (Model 23229) | | 2 | 1 | |
| 10 | 22627 | Impeller - 4" Dia Bronze - (Model 23230) | | | | 1 |
| 10 | 22675 | | 00000 | | | , |
| 100.000 | | Impeller - 3-9/16" DiaC.I (Model 23225 & 23228) | | 1 | | |
| 10 | 22673 | Impeller - 3-9/16" Dia Alum (Model 23223 & 23226) | | | 1 | 8.0 |
| 10 | 22674 | Impeller - 3-9/16" Dia Bronze - (Model 232) | 24 & 23227) | | | 1 |
| 15 | 22677 | Drive Sleeve, 7/8" Dia. shaft (Models 23223, 2 | 3224. | | | |
| | | 23225, 23229, 23230 and 23231) | | 1 | 1 | 1 |
| 15 | 22676 | Drive Sleeve, 5/8" Dia. shaft (Models 23226, 2 | 3227 | | | |
| | | and 23228) | | 1 | 1 | 1 |
| 2 | 21163 | Impeller Drive Key - S.S #6 | | 1 | 1 | 1 |
| 9 | 22621 | Impeller Locknut - S.S 1/2" | | 1 | 1 | |
| 9 | 22629 | Impeller Locknut - Br 1/2" | | | •2.6 | 1 |
| | | | | | | 200 |
| EAL | | | | | | |
| 7 | 22272 | Seal Assembly Inc.: | | 1 | 1 | 1 |
| 11 | 22133 | Seal Spring Retainer | | 1 | 1 | 1 |
| | | | | | | |
| . Per (| 23002 | Clamp Assembly for 5/8" Shaft | | | | |
| | | (Models 23226, 23227 & 23228) | | 1, | 1 | 1 |
| 8 | | Clamp | | 2 | 2 | 2 |
| 16 | 21264 | Capscrew - S.S 5/16" | | 2 | 2 | 2 |
| 5 | 21284 | Hex Nut - S.S 5/16" | | 2 | 2 | 2 |
| 18 | 21284 | Lockwasher - S.S 5/16" | | 2 | د 2 | 2 |
| 10 | 21230 | LOOK#dandr - 0.0 0/10 | | 6 | 2 | 6 |
| | 23003 | Clamp Assembly for 7/8" Shaft (Models 2322 | 3. | | | |
| | | 23224, 23225, 23229, 23230 & 23231) | | 1 | 1 | 1 |
| 8 | | Clamp | | 2 | 2 | 2 |
| 16 | 21264 | Capscrew - S.S 5/16" | | 2 | 2 | 2 |
| 5 | 21284 | Hex Nut - S.S 5/16" | | 2 | 2 | 2 |
| 18 | 21238 | Lockwasher - S.S 5/16" | | 2 | 2 | 2 |
| ····· | ····· | | | | | |
| | | tanta la lanc | | 3 | | |
| DAPTC | 22671 | Adaptor - Cast Iron | | 1 | | |
| 14 | | | | | 1 | |
| an a gala an a gala an an a gala an | 22669 | Adaptor - Aluminum | | | | |
| 14 | | Adaptor - Aluminum Adaptor - Bronze | | | | 1 |
| 1 4 1 4 | 22669 | | | 4 | 4 | 1 4 |



.



