COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR								
1	Manufacturer: Gardne	r Denver						
	Model Number: Ultima		Date:	05/11/21				
2	X Air-cooled Water-cooled			Type:	Screw			
	Lubricated X Oil Free			# of Stages:	2			
3*	Full Load Operating Pressure	ull Load Operating Pressure b			psig b			
4	Drive Motor Nominal Rating		89		hp			
5	Drive Motor Nominal Efficiency		97.0	percent				
6	Fan Motor Nominal Rating (if applicable)		0.78, 2X 3.75	hp				
7	Fan Motor Nominal Efficienc	n Motor Nominal Efficiency		percent				
8*	Input Power (kW)		Capacity (acfm) ^{a,d}		Specific Power (kW/100 acfm) ^d			
	152.14		701.4	21.69				
	133.34		615.5	21.66				
	116.18		529.6	21.94				
	100.72		443.7		22.70			
	85.91		357.8	24.01				
	72.12	·····	271.9		26.53			
9*	Total Package Input Power at Zero Flow c, d		8.4		kW			
10	35.00 30.00 25.00 15.00 10.00 20.00 300.0 400.0 500.0 600.0 700.0 800.0 Capacity (ACFM) Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity							

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$\underline{\mathbf{m}}^3 / \underline{\mathbf{min}}$	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2

12/19 R3

This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: U75-160B