

POSITIVE DISPLACEMENT VACUUM PUMPS

TriFlow® Industrial Series



TriFlow[®]: the Choice of Leading OEMs

Gardner Denver is shaping the standards of performance and reliability in the design of positive displacement blowers and vacuum pumps. The tradition continues with the TriFlow Series vacuum pumps. Each TriFlow is engineered for a wide range of commercial and industrial applications. Specifically, TriFlow is the choice of leading Original Equipment Manufacturers (OEMs) of truck mounted vacuum cleaning systems.

TriFlow Offers Operators Significant Benefits & Advantages

- Great performance and efficiency in a compact design
- Quiet operation
- Highest quality materials and construction
- Flexible installation capability
- Reduced maintenance
- Available in 3 sizes: 406, 408 & 410
- TriFlow delivers:
 - Vacuum to 16 inHg
 - Flows to 700 cfm

Quiet Operation

- Three lobe impeller geometry allows higher throughput while creating lower pulsation levels than two lobe units, resulting in reduced noise
- An internal feedback porting arrangement contributes to the further reduction of noise

Quality Promise

- Backed by one of the largest distributor networks in the industry
- Every TriFlow vacuum pump is built under rigid ISO 9001:2000 quality standards
- Each TriFlow is individually tested to meet rigorous performance specifications
- Warranty Period
 - 18 months from the date of shipment or
 - 12 months from the date of installation, whichever occurs first





Each model incorporates the following for longer service life, reduced downtime and maintenance

TriFlow® Models 410, 408, 406

- Highly reliable Dual Splash Lubrication
- Heavy duty bearings
- High strength timing gears
- Integral heat dissipation fins on the case to help maintain proper clearances

Oil-Free Air Delivery

- Piston ring seals are incorporated on each impeller shaft with a lip seal on the drive shaft, providing superior sealing to prevent oil leakage into the air chamber
- Independent oil sumps prevent cross contamination and allow the vacuum pump to operate safely on an incline when used in carpet cleaning applications

Flexible Installation

- Unique, integral mounting surfaces are precision machined for ease of installation and drive system alignment
- Critical mounting dimensions are similar to those of existing two lobe positive displacement vacuum pumps allowing for system upgrades
- The inlet and outlet ports include both flange and FNPT connections for ease of plumbing

TriFlow: Setting the Industry Standard

Performance Data


VACUUM


MODEL	RPM	10 inHg		12 inHg		14 inHg		16 inHg	
		CFM	ВНР	CFM	BHP	CFM	BHP	CFM	ВНР
406	1,760	127	4.4	117	5.2	106	6.0	-	-
	2,190	174	5.6	163	6.6	153	7.6	_	-
	2,620	220	6.8	210	8.1	199	9.3	_	-
	3,600	327	10.0	317	11.7	306	13.3	294	15.0
	4,000	371	11.4	361	13.2	350	15.1	337	17.0
408	1,760	190	6.3	176	7.5	161	8.7	-	-
	2,190	259	8.0	245	9.5	230	11.0	_	-
	2,620	328	9.7	314	11.5	298	13.3	_	-
	3,600	485	13.9	471	16.4	455	18.9	438	21.3
	4,000	549	15.8	535	18.5	519	21.2	502	24.0
410	1760	235	8.6	214	10.2	191	11.8	165	13.4
	2190	326	10.9	305	12.8	282	14.8	256	16.8
	2620	417	13.4	396	15.7	373	18.1	341	20.5
	3600	623	20.0	602	23.2	579	26.5	553	29.7
	4000	708	23.0	687	26.6	664	30.3	638	33.9

Performance based on inlet air at standard temperature of 68° F, an ambient pressure of 14.7 psia and 36% relative humidity. For performance at non-standard conditions, contact your authorized Gardner Denver representative.




HORIZONTAL CONFIGURATION






VERTICAL CONFIGURATION





DIMENSIONAL DATA

MODEL	MODEL 406		40	08	410		
PORT SIZE CONN.	2.5"	NPT	3″ ۱	NPT	4" NPT		
SHAFT DIAM.	1.2	25	1.:	25	1.25		
WEIGHT	LBS	KG	LBS	KG	LBS	KG	
	141	64	168	76	202	92	
DIMENSIONS	INCHES	ММ	INCHES	ММ	INCHES	ММ	
Α	5.0	127.0	5.0	127.0	5.0	127.0	
В	4.7	119.4	7.2	182.9	9.46	240.3	
С	4.2	106.7	4.2	106.7	3.73	94.7	
D	13.9	353.1	16.4	416.6	18.22	462.8	
E	3/8-16 UNC						
F	5.7	144.8	6.3	160.0	N/A	N/A	
G	2.8	71.1	2.8	71.1	2.8	71.1	
Н	4.5	114.3	4.5	114.3	4.5	114.3	
J	6.5	165.1	6.5	165.1	6.5	165.1	
K	13.0	330.2	13.0	330.2	13.0	330.2	
L	1.33	33.8	1.33	33.8	1.33	33.8	
M	6.0	152.4	6.0	152.4	6.0	152.4	
N	8.66	220.0	8.66	220.0	8.66	220.0	
0	4.33	110.0	4.33	110.0	4.33	110.0	
P	2.0	50.8	2.0	50.8	2.0	50.8	



TriFlow® Design Advantages

- **1** Dual splash lubrication for reduced maintenance intervals and superior durability
- 2 Tri-lobe impeller design reduces noise and vibration
- 3 Piston ring and shaft lip seals prevent oil leakage
- 4 Heavy duty bearings for greater reliability
- 5 High strength timing gears for longer service life
- 6 Large fins provide greater heat dissipation and clearance stability extending operating life
- 7 Machined mounting bosses for ease of installation



Genuine Gardner Denver

Parts & Lubricants

- Maintain the Gardner Denver performance advantage and reliability with Genuine GD Replacement Parts available through authorized sales and service representatives
- Protect your Gardner Denver investment with AEON® PD, the only lubricant specially formulated for all blowers in any environment
- Available for standard, food grade and extreme duty applications



The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-428-4890 www.gardnerdenver.com/gdproducts





©2019 Gardner Denver, Inc. Printed in U.S.A. PD-IND-TF 2nd Ed. 8/19

