

COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer:	Gardner Denver	
2	Model Number:	L05-7.5hp-110psi-1PH	Date: 1/4/2021
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled		Type: Screw
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free		# of Stages: 1
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}	22.0	acfm ^{a,e}
4	Full Load Operating Pressure ^b	110	psig ^b
5	Maximum Full Flow Operating Pressure ^c	117	psig ^c
6	Drive Motor Nominal Rating	7.5	hp
7	Drive Motor Nominal Efficiency	89.5	percent
8	Fan Motor Nominal Rating (if applicable)	N/A	hp
9	Fan Motor Nominal Efficiency	N/A	percent
10*	Total Package Input Power at Zero Flow ^e	2.1	kW ^e
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	5.80	kW ^d
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e	26.36	kW/100 cfm ^e

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

- NOTES:
- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
 - b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
 - c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
 - d. Total package input power at other than reported operating points will vary with control strategy.
 - e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
<u>m³ / min</u>	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	



Member

ROT 030.2