

UPGRADE FOR NEW & EXISTING LIQUID RING COMPRESSORS

## **GARO®** Heading Fan Kit

Designed for both, single and double stage units. The rotating fan and specially designed blades help to cool the thrust bearing and the surrounding area, extending the life expectancy of the bearings and reliability of the compressor.

The fan is fitted to the coupling hub of the GARO compressor and uses the mechanical rotation of the shaft - no additional power required.

- Lowers Thrust Bearing Temperatures
- Enhances Compressor Reliability
- Extends Compressor Life Expectancy
- Reduces Necessity of Inspections and Increases MTBM
- Does Not Require Additional Electrical Connections - Exploiting the Rotating Power of the Shaft







Via Pompei, 15 20052 Monza MB Italy +39 039 839601

www.GDGaro.com

©2018 Garo GDG-ENHANCEDBB-1160 1st Ed. 02/18



Please recycle after use.