2AV1 Liquid Ring Vacuum Pumps





Available in cast iron construction, the 2AV1 family provides capacities up to 600 m 3/h (360 CFM) in a compact monoblock design.

Space-saving installation

When compared to conventional pumps, the 2AV1's monoblock design delivers the benefits of a simple, compact and economical installation. Since the pump and motor are integral and self supporting, there is no need for additional baseplates, couplings or guards, which add to the cost, complexity and overall size of the installation.

Rugged and reliable

We focused on durability and dependability when we developed these liquid-ring pumps. With a reinforced stainless steel shaft and sealed bearings, the 2AV1 can provide up to 20,000 hours of maintenance-free operation.

Quiet operation

The 2AV1 is expertly designed and manufactured to be quiet and vibration free. With sound pressure levels of less than 75 dBA, it complies with the strictest noise standards, eliminating the need for additional sound attenuating devices.

Advantages at a glance

- Compact
- Rugged design for reliable operation and long service life
- Precision-balanced rotor
- 60 Hz motors, UL recognized components
- Available from stock
- Low installation costs
- Easy to service
- Standard mechanical seal
- Reinforced stainless-steel shaft in the pump body

Performance 110~161

25

Performance 060 ~ 071

2AV1 071


2AV1 070

2AV1 061

2AV1 060

CFM 0

M³/Hr O



75

100

125


150


Main applications

- Plastics industry
- Chemical industry
- Medical technology
- Food and beverage industry
- General industry

2AV1 Liquid Ring Vacuum Pumps







Dimensions

mm in blue

Pump	А	В	С	Inlet	Outlet		
2AV1 060	17.9	7.3	7.3	1 in. FLG.	1 in. FLG.		
	455	185	185	25 mm FLG.	25 mm FLG.		
2AV1 061	19.7	7.3	7.7	1 in. FLG.	1 in. FLG.		
	500	185	196	25 mm FLG.	25 mm FLG.		
2AV1 070	21.5	8.8	8.8	1.5 in. FLG.	1.5 in. FLG.		
	546	224	224	38 mm FLG.	38 mm FLG		
2AV1 071	25.3	8.8	10.0	1.5 in. FLG.	1.5 in. FLG.		
	643	224	254	38 mm FLG	38 mm FLG		

All dimensions are approximate

Dimensions mm in blue

Pump	А	В	С	Inlet	Outlet
2AV1 110	25.3	13.4	14.2	2 in. FLG.	2 in. FLG.
	643	340	361	50 mm FLG.	50 mm FLG
2AV1 111	28.3	13.4	14.6	2 in. FLG.	2 in. FLG.
	719	340	371	50 mm FLG.	50 mm FLG.
2AV1 121	33.0	15.0	15.6	2.5 in. FLG.	2.5 in. FLG.
	838	381	396	64 mm FLG.	64 mm FLG.
2AV1 131	38.4	15.0	17.0	2.5 in. FLG.	2.5 in. FLG.
	975	381	432	64 mm FLG.	64 mm FLG.
2AV1 161	41.1	17.7	20.5	3 in. FLG.	3 in. FLG.
	1044	450	521	76 mm FLG.	76 mm FLG.

