A Gardner Denver Product

MODEL N991-32 SERIES D.C.

# **BRONZE CLOSE COUPLED ROTARY GEAR PUMPS**





# **PERFORMANCE**

					Pressure (P.S.I.)										
Motor No.	Voltage	HP		2	10	20	25	30	40	50	60	70	80	90	100
A96	12 VDC	1/10	Flow (GPM)	3.6	3.4	3.3	2.9	2.8	2.7	2.6	2.5				
			Speed (RPM)	2920	2840	2710	2670	2540	2420	2320	2260				
8105			Current (Amps)	5.1	6.9	9.1	10.3	11.0	13.5	16.5	17.5				
A89	24 VDC	1/10	Flow (GPM)	3.3	3.2	3.1	3.0	2.9	2.8						
			Speed (RPM)	2640	2590	2520	2470	2450	2390						
8030			Current (Amps)	2.5	3.2	3.9	4.5	4.6	5.2						
A97	32 VDC	1/10	Flow (GPM)	3.6	3.5	3.4	3.3	3.3	3.2	2.9					
			Speed (RPM)	2910	2850	2770	2760	2760	2680	2560					
8107			Current (Amps)	2.0	2.7	3.7	4.2	4.3	5.6	6.6					
C81	12 VDC	1/4	Flow (GPM)	1.4	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.8	0.7	0.6	0.5
			Speed (RPM)	1190	1180	1160	1150	1140	1120	1110	1090	1070	1050	1040	1030
8295			Current (Amps)	3.1	3.7	5.0	5.2	5.8	7.2	8.5	10.2	11.3	12.6	13.6	15.0
C82	24 VDC	1/4	Flow (GPM)	3.0	3.0	2.9	2.8	2.7	2.7	2.6	2.6				
I			Speed (RPM)	2450	2450	2450	2450	2340	2340	2340	2340				
8295			Current (Amps)	3.8	4.4	5.0	5.2	6.9	7.4	8.3	8.9				

Notes: Maximum recommended operating point

#### **FEATURES**

- Compact design eases installation and use in limited space areas.
- · Construction is bronze and stainless steel wetted components.
- · Close tolerance design allows for consistent performance.
- Self-Lubricating Bearings
- Complete Units Available
- · Slotted Motor Base with Rubber Grommets
- · Permanent Magnet Rigid Base Motors
- 3/8 Ports

### GENERAL DESCRIPTION

Pump housings and gears are made of top quality bronze, shafts are 303 stainless steel. Bearings are designed of high performance carbongraphite material selected for wear resistance and long service life.

Gear pumps are positive displacement pumps. Each shaft revolution displaces a definite amount of liquid relatively unaffected by the back pressure in the discharge line. Shaft speed and flow are directly proportional.

#### LIQUIDS AND TEMPERATURE

Compact DC portable units convienient for on site servicing of vehicles, machinery and field equipment. For pumping oil direct from crankcase or oil resevoir, drums, containers, transfer diesel fuel to vehicles, pumping other liquids and chemicals compatible with materials of construction. Pumping viscous oils, SAE 30 or greater, can overload motor. Intermittent use is recommended when pumping viscous oils, especially in cold weather.

Service life will be increased substanially if liquid pumped is clean and has lubricity value. These pumps have extremely close tolerances. Fine abrasives like sand, silt or powders in suspension will destroy pumping ability.

Liquids compatible with bronze, stainless steel and the Buna lip seal can be pumped. For solvents a Viton lip seal is available. For a Viton(R)\* Seal, add S5 to the pump model number. See chemical compatibility table.

Temperature extremes are detrimental to service life and should be avoided. Basic metals of construction allow temperature range of -40° to 400°F. Standard Buna lip seal has a temperature limit of 250°F, while the VIton lip seal will handle up to 300°F. Freezing liquid in the pump can deform or damage the pump.

#### **SUCTION LIFT**

As a general rule, the suction lift should be kept at an absolute minimum by placing the pump as close to the liquid source as possible. A gear pump in new condition can lift 20 feet of water in the suction line. A foot valve (preferably with builtin strainer) is recommended at the beginning of the suction line. For a first start-up, the pump should be primed to avoid dry running. Minimum size of the suction pipe is the size of the pump inlet port. For longer suction lines (over 3 feet) or for viscous liquids, the pipe should be at least one size or two sizes larger than the pump inlet port.

## **ROTATION AND RELIEF VALVE**


If the discharge line contains any throttling devices such as a shut-off valve, a spray nozzle or other restrictive device, it is necessary to have a relief valve in the system which returns the liquid to the suction side or to the tank. The relief valve is also available as part of the pump itself (R-model pumps). However, built-in relief valves are only good for intermittent service. If used continuously, the pump will overheat. A built-in relief valve is strictly a safety device against overpressure. It will not work successfully as a pressure or flow control device. For this purpose a separate relief valve in the pressure line must be used.

Unless otherwise specified, the pump motor unit is supplied by the factory for shaft rotation counterclockwise from shaft end. Reversing motor will reverse "in and "out" ports and also requires changing relief valve location. The relief valve is always on the inlet side of this pump series. The factory pressure setting is 50 PSIG. To increase pressure, turn the relief valve adjusting screw in a clockwise direction.



# BRONZE CLOSE COUPLED ROTARY GEAR PUMPS

# **EXPLODED VIEW AND PARTS LIST**



# Pump Parts

	1	2	3*	4	5*	6*	7*	8	9*#	10	11	12	13	14	15	16	17	18
Pump No.	Screw	Body	O-Ring	Dowel Pin	Bearing	Drive Gear Assy	Idle Gear Assy	Cover	Lip Seal	Coupling	Screw	Plug Nut	Ball	Spring	Adj. Screw	Locknut	Bypass Nut	Fiber Washer
	6 Req'd	1 Req'd	1 Req'd	2 Req'd	4 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	1 Req'd	3 Req'd
N991-32	7733	9300NC5N	9797-033	8885	5024	32149	32110	9303NN2N	5007	5604	5595	N/A	N/A	N/A	N/A	N/A	N/A	N/A
N991R-32	7733	9300NC5N	9797-033	8885	5024	32149	32110	9303NN2B	5007	5604	5595	1838	5803	1840	5237	5240	5239	6533

<sup>\*</sup>Repair Kit contains items 3, 5, 6, 7 & 9. Repair Kit for N991(R) is #10640.

#### **Motor Parts**

	20	21	22	23a	23b	24	25	26	27
Motor No.	Spider	Coupling Half	Bracket/ Adapter	Screw	Screw	Lock Washer	Grommet	Motor	Adapter Kit
	1 Req'd	1 Req'd	1 Req'd	2 Req'd	4 Req'd	2 Req'd	4 Req'd	1 Req'd	1 Req'd
A96	7839	7714	7362	7424		5656	6650	8105	12091
A89	7839	7714	7362	7424		5656	6650	8030	12091
A97	7839	7714	7362	7424		5656	6650	8107	12091
C81	7839	7643	7602		5916			8295	12144
C82	7839	7643	7602		5916			8295	12144

# RECOMMENDED WIRE SIZE AND LENGTH AWG WIRE SIZE AND MAXIMUM LENGTH IN FEET

	NO.14	NO.12	NO.10	NO.8
12 VOLT DC	11 FT.	18 FT.	28 FT.	45 FT.
24 VOLT DC	20 FT.	34 FT.	55 FT.	87 FT.
32 VOLT DC	35 FT.	56 FT.	91 FT.	144 FT.

5/06

Specifications are subject to change without notice.