COMPRESSOR DATA SHEET



In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR Manufacturer: **Gardner Denver** 1 Model Number: **STG2-60hp-100psi** Date: 1/4/2021 2 Air-cooled Water-cooled Screw Type: # of Stages: Rated Capacity at Full Load Operating Pressure a, e acfm^{a,e} 3* 305.0 Full Load Operating Pressure b 4* 100 psig Maximum Full Flow Operating Pressure c psig^c 5 100 **Drive Motor Nominal Rating** 6 **60** hp **Drive Motor Nominal Efficiency** 7 95 percent Fan Motor Nominal Rating (if applicable) 8 1.2 hp Fan Motor Nominal Efficiency 9 82.5 percent Total Package Input Power at Zero Flow^e kW^e 10* **16.6** Total Package Input Power at Rated Capacity and Full Load kW^d 11 **54.90** Operating Pressure^d Package Specific Power at Rated Capacity and Full Load Operating 12* **18.00** $kW/100 cfm^e$ Pressure Isentropic Efficiency 73.84 13 Percent

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program:

<u>www.cagi.org</u>

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured
- for this data sheet.

 Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

	Volume Flow Rate at specified conditions	Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m ³ / min	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 030.1

Member

12/19 Rev 3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: ST40-60G2C