Certificate Number: 17-HS1653394-PDA 22/MAR/2018



Confirmation of Product Type Approval

Please refer to the "Service Restrictions" shown below to determine if Unit Certification is required for this product.

This certificate reflects the information on the product in the ABS Records as of the date and time the certificate is printed.

Pursuant to the Rules of the American Bureau of Shipping (ABS), the manufacturer of the below listed product held a valid Manufacturing Assessment (MA) with expiration date of 27-JUL-2022. The continued validity of the Manufacturing Assessment is dependent on completion of satisfactory audits as required by the ABS Rules.

And; a Product Design Assessment (PDA) valid until subject to continued compliance with the Rules or standards used in the evaluation of the product.

The above entitle the product to be called Product Type Approved.

The Product Design Assessment is valid for products intended for use on ABS classed vessels, MODUs or facilities which are in existence or under contract for construction on the date of the ABS Rules used to evaluate the Product.

ABS makes no representations regarding Type Approval of the Product for use on vessels, MODUs or facilities built after the date of the ABS Rules used for this evaluation.

Due to wide variety of specifications used in the products ABS has evaluated for Type Approval, it is part of our contract that; whether the standard is an ABS Rule or a non-ABS Rule, the Client has full responsibility for continued compliance with the standard.

Product Name: Pump, Centrifugal Self-Priming Model Name(s): HHLF 1.5, HHLF 2.0 & HHLF 2 HO

Presented to:

MP PUMPS INC. 34800 BENNETT DRIVE MI 48026 United States

Intended Service: Marine & Offshore Application - Bilge Systems, Ballast Systems, Fire Systems,

Cooling Water Systems, General Service and Sanitary Systems.

Description: High Head Low Flow Centrifugal Self Priming Pump with 1.5" and 2" NPT

Connections. Pump can be pedestal mounted or close coupled, Cast Iron or Bronze Construction. HHLF 1.5: Size: 1.5" x 1.5" (Suction & Discharge) Impeller Diameter: 6.7" Speed: 3450 RPM HHLF 2.0: Size: 2" x 2" (Suction & Discharge) Impeller Diameter: 6.7" Speed: 3450 RPM HHLF 2 HO: Size: 2" x 2" (Suction &

Discharge) Impeller Diameter: 7.5" Speed: 3450 RPM

Tier: 3

Ratings: HHLF 1.5: Flow Capacity: up to 150 GPM Total Head: up to 190 feet of water

HHLF 2.0: Flow Capacity: up to 150 GPM Total Head: up to 190 feet of water HHLF 2 HO: Flow Capacity: up to 150 GPM Total Head: up to 250 feet of water

Service Restrictions:i) Unit Certification is required for this product if the Pumps are used for services

listed in Steel Vessels Rules 4-6-1/7.3.1, hydrostatic and Capacity testing is to be performed to the satisfaction of the Surveyor as indicated in Steel Vessels Rules 4-6-1/7.3.2 a), b). ii) Regarding Certification details for Mobile Offshore Drilling

Units, please refer to 6-1-6/Table 1.

Comments: i) The Manufacturer has provided a declaration about the control of, or the lack of

Asbestos in this product. ii) Motors are not included in this PDA.

Certificate Number: 17-HS1653394-PDA

Notes / Documentation: Supporting Data: Dwg. No. 36194, Rev.-, HHLF Assembly C/N 3140 - Capacity

Curves Size 2" x 2" Dwg. No.38049, Rev.-, Impeller-Mach Dwg. No.38051, Rev.-, Volute-Mach Dwg. No.35764, Rev.-, HHLF2.0 PPK C: 6.7IMP C/N 3124- Capacity Curve Size 2" x 2" Dwg. No 38093, Rev.-, HHLF2HO PPK C: 7.5IMP Dwg. No. 35109, Rev.-, HOUSING (MACH) C/N 3125- Capacity Curve Size 1.5" x 1.5" HHLF 1.5, Description HHLF 2.0, Description HHLF 2 HO, Description

Term of Validity: This Product Design Assessment (PDA) Certificate 17-HS1653394-PDA, dated

28/Jul/2017 remains valid until 27/Jul/2022 or until the Rules or specifications used in the assessment are revised (whichever occurs first). This PDA is intended for a product to be installed on an ABS classed vessel, MODU or facility which is in existence or under contract for construction on the date of the ABS Rules or specifications used to evaluate the Product. Use of the Product on an ABS classed vessel, MODU or facility which is contracted after the validity date of the ABS Rules and specifications used to evaluate the Product, will require re-evaluation of the PDA. Use of the Product for non ABS classed vessels, MODUs or facilities is to be to an agreement between the manufacturer and intended client.

ABS Rules: 2017 Steel Vessels Rules 1-1-4/7.7, 1-1-A3, 1-1-A4, 4-6-1/7.3.1, 4-6-1/7.3.2; 2017

Mobile Offshore Drilling Unit Rules 1-1-4/9.7, 1-1-A2, 1-1-A3, 4-2-2/3, 4-2-4/7,

6-1-6/Table 1, 6-1-6/5.11

National Standards: International Standards: Government Authority:

EUMED: Others:

None

Model CertificateModel Certificate NoIssue DateExpiry DatePDA17-HS1653394-PDA09-AUG-201727-JUL-2022

ABS Programs

ABS has used due diligence in the preparation of this certificate and it represents the information on the product in the ABS Records as of the date and time the certificate was printed. Type Approval requires Drawing Assessment, Prototype Testing and assessment of the manufacturer's quality assurance and quality control arrangements. Limited circumstances may allow only Prototype Testing to satisfy Type Approval. The approvals of Drawings and Products remain valid as long as the ABS Rule, to which they were assessed, remains valid. ABS cautions manufacturers to review and maintain compliance with all other specifications to which the product may have been assessed. Further, unless it is specifically indicated in the description of the product; Type Approval does not necessarily waive witnessed inspection or survey procedures (where otherwise required) for products to be used in a vessel, MODU or facility intended to be ABS classed or that is presently in class with ABS. Questions regarding the validity of ABS Rules or the need for supplemental testing or inspection of such products should, in all cases, be addressed to ABS.