COMPRESSOR DATA SHEET



In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Fixed Speed MODEL DATA - FOR COMPRESSED AIR Manufacturer: **Gardner Denver** 1 Model Number: **STG2-125hp-125psi** Date: 1/4/2021 2 Air-cooled Water-cooled Screw Type: # of Stages: Rated Capacity at Full Load Operating Pressure a, e acfm^{a,e} 3* 630.0 Full Load Operating Pressure b 4* 125 psig Maximum Full Flow Operating Pressure c psig^c 5 125 **Drive Motor Nominal Rating** 6 125 hp **Drive Motor Nominal Efficiency** 7 95.4 percent Fan Motor Nominal Rating (if applicable) 5 8 hp Fan Motor Nominal Efficiency 9 85.5 percent Total Package Input Power at Zero Flow^e kW^e 10* 32.2 Total Package Input Power at Rated Capacity and Full Load kW^d 11 114.70 Operating Pressure^d Package Specific Power at Rated Capacity and Full Load Operating 12* 18.21 $kW/100 cfm^e$ Pressure

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program:

<u>www.cagi.org</u>

82.50

Percent

NOTES:

13

Isentropic Efficiency

- a. Measured at the discharge terminal point of the compressor package in accordance with
- ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.

 C. Maximum pressure attainable at full flow, usually the unload pressure setting for load control or the
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

| | Volume Flow Rate at specified conditions | Volume Flow Rate | Specific Energy Consumption | No Load / Zero Flow Power |
|---|--|------------------|--------------------------------|------------------------------|
| $\underline{\mathbf{m}^3 / \mathbf{min}}$ | ft ³ / min | % | % | % |
| Below 0.5 | Below 17.6 | +/- 7 | +/- 8 | +/- 10% |
| 0.5 to 1.5 | 17.6 to 53 | +/- 6 | +/- 7 | |
| 1.5 to 15 | 53 to 529.7 | +/- 5 | +/- 6 | |
| Above 15 | Above 529.7 | +/- 4 | +/- 5 | |

Member

12/19 Rev 3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: ST125-200G2A

ROT 030.1