## **Performance Data**

| MODEL | RPM   | VACUUM |      |        |      |        |      |        |      |
|-------|-------|--------|------|--------|------|--------|------|--------|------|
|       |       | 10 "HG |      | 12 "HG |      | 14 "HG |      | 16 "HG |      |
|       |       | CFM    | ВНР  | CFM    | ВНР  | CFM    | ВНР  | CFM    | ВНР  |
| 406   | 1,760 | 127    | 4.4  | 117    | 5.2  | 106    | 6.0  |        |      |
|       | 2,190 | 174    | 5.6  | 163    | 6.6  | 153    | 7.6  |        |      |
|       | 2,620 | 220    | 6.8  | 210    | 8.1  | 199    | 9.3  |        |      |
|       | 3,600 | 327    | 10.0 | 317    | 11.7 | 306    | 13.3 | 294    | 15.0 |
|       | 4,000 | 371    | 11.4 | 361    | 13.2 | 350    | 15.1 | 337    | 17.0 |
| 408   | 1,760 | 190    | 6.3  | 176    | 7.5  | 161    | 8.7  |        |      |
|       | 2,190 | 259    | 8.0  | 245    | 9.5  | 230    | 11.0 |        |      |
|       | 2,620 | 328    | 9.7  | 314    | 11.5 | 298    | 13.3 |        |      |
|       | 3,600 | 485    | 13.9 | 471    | 16.4 | 455    | 18.9 | 438    | 21.3 |
|       | 4,000 | 549    | 15.8 | 535    | 18.5 | 519    | 21.2 | 502    | 24.0 |
| 410   | 1760  | 235    | 8.6  | 214    | 10.2 | 191    | 11.8 | 165    | 13.4 |
|       | 2190  | 326    | 10.9 | 305    | 12.8 | 282    | 14.8 | 256    | 16.8 |
|       | 2620  | 417    | 13.4 | 396    | 15.7 | 373    | 18.1 | 341    | 20.5 |
|       | 3600  | 623    | 20.0 | 602    | 23.2 | 579    | 26.5 | 553    | 29.7 |
|       | 4000  | 708    | 23.0 | 687    | 26.6 | 664    | 30.3 | 638    | 33.9 |

Performance based on inlet air at standard temperature of 68° F, an ambient pressure of 14.7 psia and 36% relative humidity. For performance at non-standard conditions, contact your authorized Gardner Denver representative.