

COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer: Gardner Denver		
2	Model Number: VST180-120hp(2S)-125psi		Date: 01/04/21
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type: Screw
	<input checked="" type="checkbox"/> Lubricated	<input type="checkbox"/> Oil Free	# of Stages: 2
3*	Full Load Operating Pressure ^b	125	psig ^b
4	Drive Motor Nominal Rating	2 x 120	hp
5	Drive Motor Nominal Efficiency	94.0	percent
6	Fan Motor Nominal Rating (if applicable)	NA	hp
7	Fan Motor Nominal Efficiency	NA	percent
8*	Input Power (kW)	Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	234.48	1285.0	18.25
	195.05	1092.3	17.86
	156.22	899.5	17.37
	121.18	706.8	17.15
	90.46	514.0	17.60
	60.90	315.0	19.33
9*	Total Package Input Power at Zero Flow ^{c, d}		kW
10	<p align="center">Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</p>		

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator
 Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
<u>m³ / min</u>	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2