
Evacuator™

Operating Diagram



Specifications

150 psi Evacuator Unit: Part Number 7003108 450 psi Evacuator Unit: Part Number 7003110

Weight: 13 lbs. Height: 10¼"

Width: 95%" Depth: 7½"

Voltage: Not required

Operating Pressure: 150 psi maximum/450 psi

maximum

Operating Temperature: 34°F to 150°F Capacity: 52 oz. static, 42 oz. discharge

Reservoir Material: Aluminum and composite

Ball Valve Port: 1/2" Stainless Steel ball stem, double

viton "O" rings, nickel-plated brass body

Installation kit = $\frac{1}{4}$ " nylon tubing (10') threaded

fittings (2)

Optional Equipment

Manual By-Pass Button Kit: Part Number 7001772

Float Alarm Kit: Part Number 7001770 Cycle Counter Kit: Part Number 7001771



- + Full 3-Year Warranty Greatly exceeds standard one-year promises
- Pneumatic Actuation Permits installation anywhere without concerns for electrical safety issues
- Non-Magnetic Means no magnets to attract metallic trash and cause fouling
- + Energy Efficient no wasted air to increase operating costs
- + Automatic Operates on demand and does not require constant monitoring or adjustments
- + 52 oz. Static Capacity Meets the demands of almost any application and its capacity is 40% more than other models
- + 5%" Ports Substantially minimizes clogging problems
- + Self-Purging Gives trouble-free, maintenance-free performance
- + Corrosion Resistant Construction Permits installation in most hostile environments
- + Trunion-Mounted Actuator Reduces side pressure and wear, while increasing ball valve life
- + Shear-Action Ball Valve Ensures durable performance

