COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Displacement

MODEL DATA - FOR COMPRESSED AIR									
1	Manufacturer:	Gardner Denver							
	Model Number: SAV-500hp-EAY-125psi			Date:	01/04/21				
2	Air-cool	ed X Water-cooled		Type:	Screw				
	X Lubricat	ed Oil Free		# of Stages:	1				
3*	Full Load Operat	Full Load Operating Pressure b		•	psig b				
4	Drive Motor Nominal Rating		500	hp					
5	Drive Motor Nominal Efficiency		96.2	percent					
6	Fan Motor Nominal Rating (if applicable)		N/A	hp					
7	Fan Motor Nomi	nal Efficiency	N/A		percent				
8*	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) d					
	434.4		2118	20.51					
	402.3		1906	21.11					
	346.1		1483	2	23.34				
	299.4		1059		28.27				
	285.5		847	33.71					
9*	Total Package Input Power at Zero Flow c, d		69.3	kW					
10	Specific Power (kW/100 ACFM)	Note: Y-Axis Scale, 10 to 35	1000 1500 Capacity (ACFM) visual representation of the data in , + 5kW/100acfm increments if neces , 0 to 25% over maximum capacity		2500				

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	Zero Flow Power
$\underline{\mathbf{m}}^3 / \underline{\mathbf{min}}$	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 032.2

6/20 Rev2 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: EAY99J