

FLOMAX 40

4" x 4" Self Priming Centrifugal Pump

FLOMAX® 40 self-priming centrifugal pumps are capable of creating vacuum sufficient to lift liquids from heights up to 25 feet above the source. Once primed, the pump's built in flapper valve will maintain a full column of liquid in the suction line.

A FLOMAX® 40 PumPAK® is a fully assembled and run tested pump end that can be easily coupled to a number of drivers such as 215JP frame motors and gas engines. A bearing pedestal is also available for T-frame motor or belt drive.

Standard features include stainless steel drive sleeve, stainless steel fasteners, renewable wear plate, and a semi-open dynamically balanced impeller. Options include double grease-lubricated seals, stainless steel impeller and seals for all types of abrasive and/or corrosive services.

The FLOMAX® series of pumps are commonly used in Industrial, OEM, Agricultural and Marine applications, such as: Bilge Pumps, Auxiliary Fire Pumps, Ballast Transfer Pumps, Washdown Pumps, Fertilizer and Pesticide Pumps, Applicators & Sprayers, Blending Pumps, Nurse Tanks, Bulk Transfer Pumps and much more.

ABS Type Approval for the Flomax 40 - Download PDF



Suction And Discharge 4" x 4" NPT

Materials Of Construction Cast iron

Flow Up to 750 GPM

Head Feet Up to 225'

Impeller 7.75" max diameter - semi open

Motor Up to 50 HP

Drive Options Pedestal, PumPAK® (without motor)

Seal Special seal material combinations

available (consult factory), Standard

carbon / ceramic / Viton

Max Solid Size .65"





Application

- Agricultural
- Industrial
- Marine
- OEM


Features


- Renewable wear plate
- Stainless steel drive sleeve
- Stainless steel fasteners
- Up to a 25' suction lift














ITEM NO.	PART NO.	DESCRIPTION	QTY.		ITEM NO.	PART NO.	DESCRIPTION	QTY.
1	22461	HEX NUT STL - 5/8-11	16		18	26675	WASHER S.S 1.7 X .516 X .25	1
2	26258	LOCKWASHER STL 5/8	16	*	19	27403	GASKET- RULON	1
3	27201	FLANGE INLET/OUTLET	2		20	28149	IMPELLER D - 7.75" DIA.	1
4	21242	CAPSCREW S.S 5/16-18 X 7/8"	1	*	21	26685	SEAL ASSY 1.75" - VITON	1
5	21238	LOCKWASHER S.S 5/16	1	*	22	27758	GASKET - HOUSING	1
6	41821	CHECKVALVE WEIGHT STL.	1		23	35706	ADAPTER C.I MECH. SEAL	1
* 7	40690	GASKET- CHECKVALVE	1		24	26661	ADAPTER C.I.	1
8	40556	CHECKVALVE WEIGHT- UPPER	1		25	21254	LOCKWASHER S.S 1/2"	8
9	27206	STUD ZPS 5/8-11 X 3"	16		26	21246	CAPSCREW S.S 1/2-13 X 1.25	8
10	35704	HOUSING D	1		27	21274	CAPSCREW S.S 3/8-16 X 1.25	9
* 11	27204	GASKET - DISCHARGE - NI-2086	1		28	21266	LOCKWASHER S.S 3/8"	14
12	27205	PIPE PLUG - 1.25" NPT	2		29	41475	PIPEPLUG STL 1/4" NPT	1
13	26686	EYE BOLT STL - 5/8-11 X 2.12"	1	*	30	33186	PED. BODY ASSY.	1
* 14	21263	ACORN NUT S.S 3/8-16	2		31	21275	CAPSCREW S.S 3/8-16 X 2.5	2
* 15	21271	ANNULAR GASKET	2		32	26667	BRACKET C.I SER 600 PED.	1
* 16	27202	WEAR PLATE STL	1		33	21268	HEXNUT S.S 3/8-16	2
17	21274	CAPSCREW S.S 3/8-16 X 1.25"	1					

^{*-} RECOMMENDED REPLACEMENT PARTS



FLOMAX 40

